

The drawing consists of two parts. The top part is a side view of the 'NYLON PLASTIC CINCH RING'. It shows a U-shaped ring with a central slot. Dimension lines indicate: 'E' for the height of the ring, 'C REF.' for the width of the central slot, and 'B' for the thickness of the ring's body. The bottom part shows a side view of a cable with a 'NYLON PLASTIC CINCH RING' clamped around it. Dimension lines indicate: 'D' for the height of the cable, 'A' for the thickness of the cable, and 'F REF.' for the length of the cable segment shown.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	MIN. in (mm)	MAX. in (mm)									
UCT3S	.63 (16.0)	3.0 (76.2)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	12.0 (305)	50 (222)	STANDARD	.59 (267)
UCT5S	.63 (16.0)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10 (27.9)	18.0 (457)	50 (222)	STANDARD	.81 (366)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

SS_27366_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES
ULTRA-CINCH HOOK & LOOP TIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .25 (.XXX) ± .030
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE NONE

DATE	6/19/02
------	---------

WOVEN NYLON
HOOK/LOOP
COLOR: BLACK

DRAWING NO.

SS-27366

DWG
A
SIZE

7	4/12/06	FAB		ADDED PART WEIGHTS	27366	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	