



AMP**RF Coax Connectors****BNC Connectors, 75 Ohm (Continued)****Bulkhead Jacks, Crimp****Hex and O Crimp**

Maximum Panel Thickness 6.1 [0.240]

Recommended Panel Cutout

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 316151-1	Part No.
179, 179A, 179B, 181, 187, 187A, Belden 9221	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-2	—	413590-8
	O Crimp	Gold	Nickel	Polyethylene	Commercial	34.93 1.375	318451-2		221221-5
AT&T KS 19224 L2, FD179 Double Braid	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-2	—	413590-4
Belden 8218	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-2	—	413590-3
	O Crimp	Gold	Nickel	Polyethylene	Commercial	34.93 1.375	58774-1	58248-3	221221-3
140, 210, 62, 62A, 62B, 59, 59A, 55B, Belden 9291, 9209, 9269	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-1	—	413590-2
	O Crimp	Gold	Nickel	Polyethylene	Commercial	34.93 1.375	58536-1	58248-2	221221-2
302, Belden 88241, 89268, Hi-Temp 62A, Times PL-62, Berk Tek BTDC-59, BTDC-62	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-1	—	413590-1
Double Shield FG-59	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-3	—	413590-6
Belden 8212, 9104, 9112, 9240, 9167, 9250, 9266, Times FM-59 (FG-59 Type with 20 AWG C.C.)	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-1	—	413590-9
	O Crimp	Gold	Nickel	Polyethylene	Commercial	34.93 1.375	58536-1	58248-2	221221-7
AT&T 734A, Belcan 9145	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-1	—	413590-7
Belden 9114, 9248	O Crimp	Gold	Nickel	Polyethylene	Commercial	34.93 1.375	58536-1		221221-1
Belden 8281, 9141, 9231, Western Electric 724, 728, 3049	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	36.83 1.450	58425-3	—	413590-5