

NOTES: UNLESS OTHERWISE SPECIFIED.

1. ALL DIMENSIONS ARE IN MM.
TOLERANCES TO BE ± 0.5 MM.

2. PARTS SPECIFIED AS FOLLOWS:






- 2-1. ENCLOSURE:
* MEET V-0 FLAMMABILITY.
* COLOR: BLACK
* TEXTURE: MOLDTECH MT11020.
- 2-2. AC INLET:
* IEC 320, C6 CERTIFIED, 3 WAY.
* COLOR: BLACK.

- 2-3. DC OUTPUT:
* PLUG SHAPE: TUNING FORK TYPE
* PLUG INSULATOR: BLACK

- * PLUG POLARITY:
* COLOR: BLACK

- 2-5. ADAPTOR UNIT:
* DIMENSIONS MARKED * MARK MUST BE
INSPECTED & CONTROLLED STRICTLY
BY OQC.

J1	WIRE	PLUG
A	WHITE	INSIDE
B	SPIRAL	OUTSIDE



TOLERANCES $\pm$		
ANGULAR	LINEAR	
0.5°	0~6	0.10
	6~30	0.20
	30~80	0.25
	80~180	0.30
	180~315	0.50
	315~800	0.8