




HLPC Series

Class 1, Div 2 Hazardous Location Photocell Assembly


Features

- Voltage Configurations
 - A) HLPC-120 for 120V applications
 - B) HLPC-208-277 for 208V through 277V applications
- 1000W, 1000VA Load Rating
- 50/60 Hz Operation
- Epoxy Encapsulation for Superior Moisture and Chemical Resistance
- One-piece molded GE Ultem 1000 translucent lens assembly, UL94V-0 compliant
- Temperature Range of -40°C to 60°C
- For use in Class 1, Division 2 applications, Groups A, B, C, and D
- Kit Includes:
 - Photocell
 - Stainless Steel 5/8" Washer
 - Stainless Steel Knurled Locknut
 - Neoprene Gasket with Adhesive Back
 - (3) High Temperature 150°C Wirenuts


The HLPC is a rugged Hazardous Location Photocell Assembly. A variety of voltages for Class 1, Division 2 applications.



Wiring



Dimensions



★ **MADE IN USA** ★
Of Imported And Domestic Components



Specifications subject to change without notice.

Rev 8-08-14