




Material

Casing: Plastic (Black) UL94V-0
Impeller: Plastic (Black) UL94V-0
Lead Wire: UL10368, AWG26, +Red, -Black

4710KL characteristic curve



4710KL panel cut out



Detailed Specifications

Expected Life:	40 degree C 50,000 Hours (L10)
DC Fan:	Ball Bearing Fan
Nominal Voltage:	24[V]
Operating Voltage Lower:	10[V]
Operating Voltage Upper:	27.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Speed:	1900[min^{-1}]
Max. Air Flow:	2.15[m^3/min]
Max. Air Flow:	75.9[CFM]
Max. Static Pressure:	24.8[Pa]
Max. Static Pressure:	0.1[$\text{In H}_2\text{O}$]
Noise:	31[dB]
Mass:	180[g]
Fan Size:	119[mm]
Fan Width:	25[mm]