



KF-E FIXED MALE CONNECTOR:



CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIA.	MIN. BORE	ACROSS FLATS	THREAD LENGTH	NOM. LENGTH
10	Pg to DIN 40430	Pg7	GAP 0101	12.5	4.8	14.0	8.0	16.5
12		Pg9	GAP 0202	15.2	7.8	17.0	8.0	21.5
16		Pg11	GAP 0303	18.6	10.9	20.0	12.0	28.0
20		Pg16	GAP 0405	22.5	14.9	24.0	12.0	28.0
25		Pg21	GAP 0506	28.3	18.9	30.0	13.5	31.0
32		Pg29	GAP 0607	37.0	25.9	40.0	15.0	33.0
40		Pg36	GAP 0708	47.0	33.9	49.6	17.0	36.0
16	Metric to BS 6053	16mm	GAM 0303	16.0	10.8	19.0	10.0	24.5
16		20mm	GAM 0304	20.0	10.8	24.0	10.0	24.5
20		20mm	GAM 0404	20.0	14.8	24.0	10.0	24.5
25		25mm	GAM 0505	25.0	18.8	30.0	12.0	28.0
32		32mm	GAM 0606	32.0	25.8	36.0	13.0	29.0
40		40mm	GAM 0707	40.0	33.8	46.0	15.0	31.5
50		50mm	GAM 0808	50.0	41.8	55.0	15.0	33.0

KF-E SWIVEL MALE CONNECTOR:



CONDUIT SIZE (mm)	THREAD TYPE	THREAD SIZE	ORDERING CODE	DIMENSIONS (mm)				
				THREAD DIA.	MIN. BORE	ACROSS FLATS	THREAD LENGTH	NOM. LENGTH
10	Pg to DIN 40430	Pg7	GBP 0101	12.5	4.8	14.0	8.0	22.0
12		Pg9	GBP 0202	15.2	7.8	17.0	8.0	30.3
16		Pg11	GBP 0303	18.6	10.9	20.0	12.0	38.0
20		Pg16	GBP 0405	22.5	14.9	24.0	12.0	38.0
25		Pg21	GBP 0506	28.3	18.9	30.0	12.0	41.0
32		Pg29	GBP 0607	37.0	25.9	40.0	15.0	46.0
40		Pg36	GBP 0708	47.0	33.9	49.6	17.0	51.0
16	Metric to BS 6053	16mm	GBM 0303	16.0	10.8	19.0	10.0	34.3
20		20mm	GBM 0404	20.0	14.8	24.0	10.0	34.3
25		25mm	GBM 0505	25.0	18.8	30.0	12.0	40.5
32		32mm	GBM 0606	32.0	25.8	36.0	13.0	41.5
40		40mm	GBM 0707	40.0	33.8	46.0	15.0	47.3
50		50mm	GBM 0808	50.0	41.8	55.0	15.0	47.0

KF-E SPACE SAVER CONNECTOR:



CONDUIT SIZE (mm)	ORDERING CODE	DIMENSIONS (mm)		
		MIN. BORE	ACROSS FLATS	NOM. LENGTH
10	GUN0101	4.8	14.0	11.5
12	GUN0202	7.8	16.0	13.5
16	GUN0303	10.8	19.0	14.5
20	GUN0404	14.8	24.0	14.5
25	GUN0505	18.8	30.0	16.0
32	GUN0606	25.8	36.0	16.0
40	GUN0707	33.8	46.0	16.0
50	GUN0808	41.8	55.0	18.0

MATERIAL: BRASS / NICKEL PLATED

PROPERTIES:

IP RATING WITH RECOMMENDED CONDUIT

IP 54 (NO INGRESS OF TALCUM POWDER AT NORMAL PRESSURE AND NO INGRESS OF WATER WITH TURNTABLE SPRAY.).

OPERATING TEMPERATURE

- 25 TO + 90° C.

FITTING INSTRUCTIONS INCLUDED WITH PRODUCT AND AVAILABLE ON REQUEST – LEAFLET No. 808853

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.