



119 x 38mm (4.7" X 1.5") AC FAN

4000N Series

Terminals
Air Intake – Over struts



AVAILABLE WITH:

HIGH PERFORMANCE
SINTEC
SLEEVE BEARING SYSTEM

4.69" X 4.69" X 1.50" AC Fan, All Metal, Air intake – Over struts

Curve	PART NUMBER	Type of Bearing	AC Volts	Hertz	Watts	CFM @ 0"		Temp. Max °C	Wgt. (oz)	Features	Approvals*		
						dBA					UL	CSA	VDE
1	4800N	Sleeve	115	50/60	9	57	32	75	18	Terminals	√	√	√
1	4850N	Sleeve	230	50/60	9	57	32	75	18	Terminals	√	√	√
2	4530N	Sleeve	115	50/60	16	89	45	65	18	Terminals	√	√	√
2	4580N	Sleeve	230	50/60	16	89	45	65	18	Terminals	√	√	√
3	4500N	Sleeve	115	50/60	15	100	48	65	18	Terminals	√	√	√
3	4550N	Sleeve	230	50/60	15	100	48	65	18	Terminals	√	√	√

* UL yellow card E38324, CSA file 27697, VDE file 1176 (4800N), VDE 6617 (4530 & 4500), 4621 (4850)

CONSTRUCTION MOUNTING & CONNECTION	Mounting:	Either face using four .169" (4.3mm) holes 18 ounces (520g)	Housing:	Metal with metal impeller Terminals with two flat pins, .118" x.02' (3.0 x 0.5 mm)
	Weight:		Connection:	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[4800X](#)