

ON/OFF
POWER SWITCH

SURGE INDICATOR
LIGHT

1783.08 mm
[70.200 in]

265.62 mm
[10.458 in]

76.20 mm TYP
[3.000 in]

27.05 mm TYP
[1.065 in]

41.05 mm
[1.616 in]

RESETABLE
CIRCUIT
BREAKER

6' FOOT
POWER CORD
(NEMA 5-15P)

29.18 mm
[1.149 in]

5.08 mm
[0.200 in]

SECTION A-A
(VIEW FROM FRONT)

ASSEMBLY - VIEW FROM END

1789.89 mm
[70.468 in]

ASSEMBLY - VIEW FROM SIDE

ISOMETRIC VIEW

1587H19**S

Finish - Case - Anodized Aluminum Extrusion

Ends - ABS Plastic

Rated - 125 VAC, 60 Hz, 15 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

CSA No. 8-M1986

Surge Specs - 780 Joules, 54000 Amps Transient Current

- Protection in 3 AC Modes (L-N, N-G, L-G)

Cord Length & Colour

1587H19A1S - 6' Foot Power Cord (NEMA 5-15P)

1587H19B1S - 15' Foot Power Cord (NEMA 5-15P)

Accessories Included

Mounting Bracket Kit with Hardware

**HAMMOND
MANUFACTURING™**
1587H19S**
www.hammondmfg.com