

CAD32G7

RELAY 600V 10AMP TESYS + OPTIONS



List Price \$62.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR43364 Class 3211 03 - CE Marked - IEC Rated
Ampere Rating	10A
Contact Material	Silver-Nickel
Contact Rating	A600 - Q600
Coil Voltage	120VAC
Maximum Voltage Rating	600VAC
Mounting Type	Din Rail(35mm)/Panel
Terminal Type	Screw Clamp
Type	TeSys D
Depth	3.66 Inches
Height	3.03 Inches
Marketing Trade Name	TeSys
Width	1.77 Inches
Contact Configuration	3 N.O./2 N.C.
Weight	1.28 Pounds

Shipping and Ordering

Category	22371 - Relays, Control, IEC
Discount Schedule	I12
GTIN	00785901204848
Package Quantity	1
Weight	0.77 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.