




DIMENSIONS: mm (In.)

SPECIFICATIONS	
Insertion & Extraction Force:	1Kg. Min
Dielectric Strength For 60 Sec:	AC 2000V Min.
Suitable Rated Current:	6.3A 250V
Insulation Resistance AT 500VDC:	100 $\mu\Omega$ Min.
Temperature Rise:	60°C Max.
Voltage Drop:	15 mV Max.
Body Material:	Flame Retardant Nylon with Fiber Glass

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-EPD2005](#)