


										1
LOC	DIST			REVISIONS						
G	14	P	F	ZONE	LTR	DESCRIPTION			DATE	APPD
					C	REV,RDRW,& SM PKG PER 0720-0040-93			3-29-93	1AP DAP



METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED
CS LR7189 Certified	MILITARY P/N AND CLASS
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP 8S AMP 12-10* APPROX AS SHOWN
8S INDICATES STUD SIZE

50	LOOSE PIECE, BOX	8-53127-2
2500	ON TAPE	53127-2
---	LOOSE PIECE	53127-1
QUANTITY	PACKAGING TYPE	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME TERMINAL, SHORT SPRING SPADE, SOLISTRAND™		
SIZE	CAGE CODE	DRAWING NO
③	00779	③=53127
SCALE	10:1	SHEET 1 OF 1

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -
MATERIAL
PHOSPHOR BRONZE
PER ASTM B-103
ANNEALED
FINISH
TIN PLATE
0.00254[.000100] MIN
THK PER MIL-T-10727

DR 3-29-93
TA BRINKMAN
CHK 3-29-93
DA PATTERSON
APPD 3-29-93
DE MILLER
APPD 3-29-93
JL MECKLEY
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT -