

Audio Line Plugs

Canare offers in-line cable mount audio plugs in a variety of configurations for the discriminating professional. Each model is carefully designed to accommodate small to large O.D. cables and all versions offer a generous soldering area for easy wiring assembly, good electromechanical characteristics, super performance and long life durability.

Applications

- Guitar / keyboards
- sound mixers
- pa systems
- Test Probes
- Hi-Fi interconnects

Features

Robust Dependable Construction
Brass with Nickel/Gold Plating
360° Crimpable Cable Strain Relief
Easy to Solder
Beautiful Long Lasting Finish

Canare F-Series audio plugs feature a proprietary 360° cable clamp design that ensures long life reliability.

All F-Series audio plugs have a beautiful nickel plated, bell brass handle with a specially designed knurled surface to prevent finger slippage. The F-09 RCA plug features an extra narrow profile body (for high density panels). The handle extends over the outer contact sleeve for improved RF shielding.

Spring type strain relief prevents cable damage due to repeated bending at the connector entry point; cable lasts three times longer than plugs without strain relief.


F-09 and F-10 plugs have a Gold plated brass inner shaft that offers low contact resistance and eliminates corrosion problems with the mating receptacle.

Canare F-15 and F-16 1/4" phone plugs use a patented "V-Lock" system that ensures good electrical contact by keeping the plugs tight where others pull out.

F-15

Reinforced one-piece body and sleeve includes a pure brass bar that runs the length of the handle; 50% stronger than ordinary plugs and 20% stronger than other high-grade plugs.

Satin-finished, nickel-plated solid brass handle, shuts out static and electromagnetic noise.



Connector Specifications										
Model	Type	Notes	Cable Entry I.D. in (mm)	* Max Cable O.D. in (mm)	Shaft material plating	Dielectric	Body material plating	Insulation tube	Cable spring plating	
F-09	RCA	Narrow profile. Body extends over contact	.248 (6.3)	.236 6.0	Brass Gold	Polyacetal	Brass Nickel	–	Nickel	
F-10	RCA	Deluxe clamp and body design	.244 (6.2)			PTFE		Black PVC		
F-11	Mini Phone TS	Tip, Sleeve	.248 (6.3)		Brass	–		–		
F-12	Mini Phone TRS	Tip, Ring, Sleeve	.244 (6.2)					Black PVC		
F-15	1/4"TS phone	Tip, Sleeve	.244 (6.2)					Nickel		
F-16	1/4"TRS phone	Tip, Ring, Sleeve								

* With Spring Removed, Max. Cable O.D. is .295in (7.5mm)