



## T120I0HSH4

Heavy Duty Cable Tie, 11.8" Long, 120lb Tensile Strength, PA66HS, Black, 500/pkg

Article Number: 111-12216

Part Number: T120I0HSH4

Type: T120I

### Base Data

|                                      |                                                                                                                                                                                                                                                                                                   |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Part No.</b>                      | T120I0HSH4                                                                                                                                                                                                                                                                                        |
| <b>Type</b>                          | T120I                                                                                                                                                                                                                                                                                             |
| <b>Color</b>                         | Black (BK)                                                                                                                                                                                                                                                                                        |
| <b>Features</b>                      | <ul style="list-style-type: none"> <li>• Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.</li> <li>• Head design provides high tensile strength with very low insertion force.</li> <li>• Bent tail ensures a quick and simple installation.</li> </ul> |
| <b>Application Method</b>            | Quick, simple fixing by hand or with HellermannTyton tensioning tools                                                                                                                                                                                                                             |
| <b>Identification Plate Position</b> | none                                                                                                                                                                                                                                                                                              |
| <b>Releasable Closure (Yes/No)</b>   | No                                                                                                                                                                                                                                                                                                |
| <b>Tie Closure</b>                   | plastic pawl                                                                                                                                                                                                                                                                                      |
| <b>Typical Application</b>           | Used to bundle and secure wire and cable.                                                                                                                                                                                                                                                         |
| <b>Variant</b>                       | Inside Serrated                                                                                                                                                                                                                                                                                   |

### Product Dimensions

|                              |                   |
|------------------------------|-------------------|
| <b>Min. Tensile Strength</b> | 120.0lbs / 535.0N |
| <b>Length (L)</b>            | 11.8" / 300.0mm   |
| <b>Width (W) (imperial)</b>  | 0.3"              |
| <b>Width (W)</b>             | 7.6mm             |
| <b>Max. Cable Tie Width</b>  | 0.30" / 7.61mm    |
| <b>Min. Ø Bundle</b>         | 0.2" / 5.0mm      |
| <b>Max. Ø Bundle</b>         | 3.2" / 80.0mm     |
| <b>Head Length</b>           | .393"             |

**Head Width** .502"

### Material and Specifications

---

**Material** Polyamide 6.6 heat stabilized (PA66HS)

**CSA Certified** No

**Flammability** UL94 V2

**Material Specification** HF

**Operating Temperature** -40 °F to +257 °F (-40 °C to +125 °C)

**ROHS Conformity**  RoHS

**Specification** UL ZODZ2.E64139

**UL Listed (US and Canada)** Yes

**UL Recognized (US and Canada)** Yes

### Logistic and Packaging

---

**Packaging Type** bag

**Pkg. Qty.** 500

**Carton Qty.** 1500

**EAN code** 4031026422312

**UPC** 089306057956