

## Specification Sheet

Part Number: 184-13005

Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.



|                |           |
|----------------|-----------|
| Article Number | 184-13005 |
|----------------|-----------|

|      |         |
|------|---------|
| Type | SLHD1X3 |
|------|---------|

|       |           |
|-------|-----------|
| Color | Gray (GY) |
|-------|-----------|

|              |        |
|--------------|--------|
| Quantity Per | carton |
|--------------|--------|

|                     |                                                                                                                                                                                                                                                        |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton Pro-Duct High-Density, Slotted-Wall Wiring Duct features narrow fingers equaling a 2 to 1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                       |
|-------------------|---------------------------------------------------------------------------------------|
| Short Description | High Density Slotted Wall Wiring Duct, 1" x 3", Non-Adhesive, PVC, Gray, 120ft/Carton |
|-------------------|---------------------------------------------------------------------------------------|

|                  |                |
|------------------|----------------|
| Global Part Name | SLHD1X3-PVC-GY |
|------------------|----------------|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 6.0 |
|---------------------|-----|

|                   |      |
|-------------------|------|
| Length L (Metric) | 1.83 |
|-------------------|------|

|                 |              |
|-----------------|--------------|
| Fixation Method | Non-Adhesive |
|-----------------|--------------|

|                    |     |
|--------------------|-----|
| Width W (Imperial) | 1.0 |
|--------------------|-----|

|                  |      |
|------------------|------|
| Width W (Metric) | 25.4 |
|------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 3.07 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 77.9 |
|-------------------|------|

|                                  |     |
|----------------------------------|-----|
| Mounting Hole Centers (Imperial) | 2.0 |
|----------------------------------|-----|

|          |                         |
|----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
|----------|-------------------------|

|                   |     |
|-------------------|-----|
| Material Shortcut | PVC |
|-------------------|-----|

|              |           |
|--------------|-----------|
| Flammability | UL 94 V-0 |
|--------------|-----------|

|              |    |
|--------------|----|
| Halogen Free | No |
|--------------|----|

|                       |    |
|-----------------------|----|
| UV Resistant (Yes/No) | No |
|-----------------------|----|

|                       |                |
|-----------------------|----------------|
| Operating Temperature | +122°F (+50°C) |
|-----------------------|----------------|

|                              |                                                  |
|------------------------------|--------------------------------------------------|
| Reach Compliant (Article 33) | No                                               |
| ROHS Compliant               | Yes                                              |
| Certification/Specification  | UL EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 CSA |
| UL Recognized (US)           | Yes                                              |
| Package Quantity (Imperial)  | 120.0                                            |
| Package Quantity (Metric)    | 36.58                                            |
| Customs Number               | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)