

KNIVES & BLADES

Stanley manufactured its first utility knife back in 1935, and it didn't take long for the world to take notice. Compact, rugged, comfortable to hold and armed with a razor-sharp blade, it quickly became an indispensable tool for a wide variety of tradesmen, fabricators and installers.

Look into virtually any toolbox, shop cabinet, workbench, tool belt or kitchen junk drawer and you'll likely find a Stanley utility knife. In fact, the tool's widespread acceptance has even received iconic status; in the United Kingdom, Australia and New Zealand, any utility knife is simply known as a Stanley knife.

It's worth noting as well that Stanley hasn't maintained its dominant market position for over 75 years by being complacent. The company has made a serious commitment to continuously redesign, refine and enhance its utility knives and blades. It now makes nearly 60 different sizes and styles of utility knives, including ones with retractable blades, fixed blades and snap-off blades. Stanley also offers several specialty knives and blades manufactured for specific tasks, such as cutting carpeting, roofing materials, acrylic sheets, plastic laminates, linoleum and even sod.

Some of the many features Stanley developed and first brought to market include its interlocking nose, which securely locks together the two knife halves for precise cutting, and an InstantChange™ design that allows you to quickly change blades without using a screwdriver to open the knife. Other features found on Stanley knives include a non-slip, sure-grip thumb rest and an integrated string cutter.

Stanley's commitment to excellence and innovation extends to its offering of induction heat-treated blades that stay sharper up to 75 percent longer than standard single-material blades. In fact, Stanley blades have become so popular, its state-of-the-art manufacturing facilities must pump out 20,000 miles of blades each and every year to keep up with demand. And with the company's devotion to innovation, design and quality, the unprecedented success of the Stanley knife will undoubtedly continue for the next 75 years.





RETRACTABLE BLADE	32-34
FIXED BLADE	34-35
SPECIALTY	36
POCKET	36-37
SAFETY	38-39
HOBBY	39
SNAP-OFF	40-41
KNIFE & BLADE SELECTION GUIDE	42
BLADES	43-47



WARNING: KNIVES ARE INTENDED FOR CUTTING ONLY AND SHOULD BE HANDLED WITH CARE.
BENDING BLADE CAN CAUSE IT TO BREAK, POSSIBLY RESULTING IN BODILY INJURY.





FatMax Xtreme® Twin Blade Knife

- 2 knives in 1 - new twin blade design allows the user to alternate between 2 blades without carrying more than 1 knife
- InstantChange™ feature allows the user to replace dull blades in seconds
- Easy access blade storage holds up to 9 blades for fast and easy blade change
- Interlocking blade sliders so that only 1 blade is extended at a time
- Rubber comfort grip minimizes fatigue and reduces slippage
- Knife includes 2 straight and 2 hook blades
- Total blade storage capacity - 11 (9 storage + 2 in use)

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-789	6-7/8	175	6	24	076174107890

FatMax® Retractable Utility Knife

- Blade wiper removes excess dirt and protects knife
- Blade clamp eliminates blade wobble, gives control
- Ergonomic design for ease of use
- Soft-touch panels/grips allow control, fewer slips
- Pop-up blade dispenser for easy access and fast changeover
- Supplied with FatMax® blades
- Push-button blade change - no tools needed



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-778	6-5/8	168	6	36	076174107784

InstantChange™ Retractable Knife

- Strong, durable construction combines a cast-metal core with bi-material soft panels for a sure grip
- Blade changes with the push of a button – no tools required
- Curved handle design for comfort, control and balance
- Swing-out blade storage for easy blade access
- Integrated string cutter and retractable slide
- Large hang hole for pegboard storage
- Padded thumb rest



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-788	6-5/8	168	6	36	076174107883

Dynagrip® Retractable Utility Knife

- Cushion grip surface for comfort, even in extreme temperatures
- Slip-resistant grip helps prevent slipping, even on angled surfaces
- Interlocking nose secures blade



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-779	5-3/8	137	6	36	076174107791

Quick Change Retractable Utility Knife

- Change blades quickly – no screwdriver required
- Three-position retractable blade slide
- Swing-out blade storage magazine
- Integrated string cutter, even when blade is retracted



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-499	6-3/8	162	6	36	076174104998

Swivel-Lock® Retractable Utility Knife

- Large 7" (178mm) handle design is comfortable for extended use
- Swivels open for "no-tools" cleaning and blade changes
- Interlocking nose secures knife halves together
- Lightweight aluminum body



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-989	7	178	6	72	076174109894

Ergonomic All-Metal Retractable Utility Knife


- No tools required – thumb screw stays attached to knife and allows for easy blade change
- Durable, simple and comfortable shape
- Narrow nose ideal for accurate cutting applications
- Blade storage in handle



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-707	7.25	184	6	36	076174107074

All-Metal Retractable Utility Knives

- Interlocking nose to hold blade securely
- Three-position retractable blade
- Contoured handle with diagonal ribs for a slip-resistant grip
- Blade storage in handle



SKU #	DESCRIPTION	LENGTH		BOX QTY	CARTON QTY	UPC
		IN.	MM			
10-079	Standard	5-7/8	150	6	36	076174100792
10-179	High-Visibility	5-7/8	150	6	36	076174101799

KNIVES



Classic 99® Retractable Utility Knife

- Interlocking nose to hold blade securely
- Three-position retractable blade
- Blade storage in handle

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-099	6	152	6	36	076174100990



Homeowner's Retractable Utility Knife

- Lightweight, economical utility knife
- Three-position retractable blade
- Interlocking overlap nose secures blade between knife halves

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-175	6-1/8	156	6	36	076174101751



Junior Classic Utility Knife

- All-metal, durable construction
- Blade storage
- Compact size

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-016	5	127	8	48	076174100167



FatMax® Fixed Blade Utility Knife

- Ergonomic design for ease of use
- Soft-touch panels/grips allow control, fewer slips
- Blade clamp eliminates blade wobble, gives control
- Pop-up blade dispenser for easy access and fast changeover
- Cartridge holds up to 5 blades
- Supplied with FatMax® blades
- Dual blade position in nose for versatility

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-780	6-1/4	160	6	36	076174107807

Swivel-Lock® Fixed Blade Knife

- 6" (152mm) handle length
- Handle swivels open for quick, easy blade change
- Interlocking nose design
- Comfortable, contoured handle
- Works with all Stanley® replacement utility blades



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-399	6	152	6	36	076174103991

Ergonomic All-Metal Fixed Blade Utility Knife

- No tools required – thumb screw stays attached to knife and allows for easy blade change
- Durable, simple and comfortable shape
- Narrow nose ideal for accurate cutting applications
- Blade storage in handle



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-705	5.5	140	6	36	076174107050

Classic 199® Fixed Blade Utility Knife

- Positive fixed blade retention for heavy-duty cutting
- Super-duty cast-metal textured handle designed for long, tough use
- Nose overlaps at top and bottom for strength
- Works with all Stanley® replacement utility blades
- The original utility knife



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-209	5-3/8	137	6	36	076174102093

299® Fixed Blade Interlock® Utility Knife

- Interlocking nose
- Contoured handle with slip-resistant grip
- Blade storage integrated into handle



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-299	5-3/8	137	6	36	076174102994

KNIVES



Retractable Carpet Knife

- 6-1/2" handle length
- Retractable blade for controlling depth of cut
- Angled handle design provides easy access to hard-to-reach places
- Blade storage capacity: 10 regular-duty .015" blades
- Works with regular- (10-525) and heavy-duty (11-530) carpet blades


SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-525	6-1/2	158	6	36	076174105254



FatMax® Hook Knife

- Cuts and trims floor covering, roofing material, sod and turf grass
- Taper-ground cutlery steel blade
- Ergonomically designed slip-resistant grip
- Handle structure designed for strength and durability

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-510	5-1/2	140	6	36	076174105100



Linoleum Flooring Knife

- For cutting and trimming vinyl or linoleum floor covering, roofing and similar material
- Taper-ground cutlery steel blade permanently fastened to comfortable, hardwood handle

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-509	4-1/2	127	6	72	076174105094



SportUtility™ Outdoorsman Knife

- Alternate between two blades without carrying more than one knife

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-804	6-3/8	162	2	6	076174108040



Folding Fixed Blade Utility Knife


- One-handed open/close
- Quick no-tools blade changing
- Aluminum design is durable and lightweight
- Stainless-steel belt clip
- Accepts standard utility and hook blades

SKU #	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
		IN.	MM			
10-855	5-3/4	146	5.75	4	16	076174108552

SPECIALTY & POCKET KNIVES

QuickSlide™ Pocket Knife

- Durable all-metal, die-cast zinc construction
- Compatible with most standard utility and hook blades
- Quick no-tools blade changing
- Belt clip



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-810	5-3/4	146	6	36	076174108101

QuickSlide2 Knife

- Durable all-metal, die-cast zinc construction
- Compatible with most standard utility and hook blades
- Quick no-tools blade changing
- Belt clip



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-812	4-1/4	108	4	24	076174108125

QuickSlide™ Sport Utility Knife

- Great for multipurpose cutting, camping and outdoor activities
- 3"/75mm serrated sport blade
- Holds standard utility blades
- Quick no-tools blade changing



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-813	4-5/8	118	2	6	076174108132

Folding Pocket Knife

- Powder-coated, epoxy handle
- Blade lock
- Replaceable stainless-steel blade
- Blade folds into handle for storage



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-049	4-1/4	105	6	72	076174100495

Metal Mitey-Knife® Pocket Knife

- Rugged metal body
- Same silhouette as Stanley® Interlock® knives
- Retractable blade with two cutting positions
- Two blades and handy keychain included



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-239	2-7/8	73	12	144	076174102390

KNIVES



Self-Retracting Safety Utility Knife

- Spring-loaded blade retracts automatically when pressure on slide button is released
- Designed to be used for opening cartons
- Blade is only exposed when the knife is in use
- Interlocking nose secures blade between knife halves
- Orange color for high visibility

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-189C	5-7/8	150	6	36	076174101898



Metal Safety Knife

- Auto-retracting blade – helps reduce the chance of lacerations and puncture wounds
- 3-sided slider button – comfortable and easy to use from top, left or right side
- Easy blade change – no tools needed
- Ergonomically designed for comfortable use
- Supplied with 3 safety blades

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-781	5-5/8	143	6	36	076174107814



Retractable Hood Safety Knife

- Auto-retracting blade – helps reduce the chance of lacerations and puncture wounds
- 3-sided slider button comfortable and easy to use from top, left or right side
- Box tape splitter for convenience
- Ergonomically designed for comfortable use
- Supplied with 1 safety blade

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-783	5-1/2	140	6	36	076174107838



Folding Safety Knife

- 2-sided slider button - easy to use from left or right side
- Spring-loaded – unfolds easily
- Compact size for portability
- Box tape splitter for convenience
- Supplied with 1 safety blade

SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-784	4	102	6	36	076174107845

Utility Blade Safety Knife

- Spring-loaded auto-retracting blade – helps reduce the chance of lacerations and puncture wounds
- Reversible for left- or right-handed use
- Easy blade change – no tools needed
- Supplied with 1 blade



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-785	5	127	6	36	076174107852

Hobby Knife


- Precision hobby knife available with a strong, yet lightweight aluminum body
- Great for home, office, studio or workshop
- Positive metal barrel blade locks
- Works with standard hobby and craft blades



SKU #	LENGTH		BOX QTY	CARTON QTY	UPC
	IN.	MM			
10-401	5	127	5	50	076174104011


12 in 1 Multi-Tool

- Stainless-steel construction
- High-quality nylon holster



SKU #	TOOLS INCLUDED	LENGTH		BOX QTY	CARTON QTY	UPC
		IN.	MM			
84-519K	Long nose pliers Curve jaw pliers Wire cutter Saw Phillips® screwdriver Standard screwdrivers (1/4", 5/16", 1/8") Small knife Large knife Bottle opener File	6-1/2	165	3	12	076174845198

Phillips is a registered trademark of Phillips Screw Co.



FatMax Xtreme® Snap-Off Knife

- Die-cast all-metal construction stands up to the most extreme job site conditions
- Blade knob to lock blade in place for heavy-duty applications
- Diamond-shaped texturing provides a sure grip
- Textured die-cast finish for positive slip-resistant grip
- Stainless-steel 4-blade cartridge

SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-817	25mm	7	8-1/4	210	6	36	076174108170



FatMax® Snap-Off Knife

- Stainless-steel barrel is durable and rust resistant
- Comfortable bi-material slider with soft grip
- Removable blade snapper for removal of a worn segment
- Thumb dial clamps down on blade to minimize blade movement for control
- Instant blade release functionality for quick blade changes

SKU #	SIZE	POINTS ON BLADE	BLADE STORAGE CAPACITY	LENGTH		BOX QTY	CARTON QTY	UPC
				IN.	MM			
10-475	9mm	13	6	5-3/8	135	6	36	076174104752
10-481	18mm	8	6	7	179	6	36	076174104813
10-486	25mm	7	4	8-3/8	213	6	36	076174104868




FatMax® 18mm Snap-Off Knife

- Cast-aluminum body and stainless-steel blade channel for durability
- Slim-line design for ease of control, precision cutting and convenient storage
- Auto-locking blade slider
- Built-in blade snapper makes snapping off used segments convenient and easy
- Pocket clip - portable and easy to store

SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-421	18mm	8	6-1/4	160	6	36	076174104219

DynaGrip® Snap-Off Knife

- 25mm/1" snap-off blades are durable and resist accidental snapping
- Thumb-dial blade release makes blade change easy
- Rubber DynaGrip® panels for secure, comfortable grip



SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-425	25mm	7	7	180	6	72	076174104257

Quick-Point™ Knives

- Light-duty, retractable knife with Quick-Point™ snap-off blades
- Blade sections snap off, providing fresh, sharp cutting points
- Removable blade snapper included in cap of knife
- Pocket clip included on 10-150, 9mm Quick-Point™ Snap-Off Knife



SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-150	9mm	13	5-1/8	130	6	72	076174101508
10-151	18mm	8	6-1/8	160	6	72	076174101515

Standard Snap-Off Knife


- Made with stainless-steel and high-impact polymer components
- Smooth slider mechanism features an audible "click" and is self-locking
- Blade sections snap off to provide fresh, sharp cutting points
- Removable blade snapper included in cap of knife
- Hang hole for storage or lanyard
- High-visibility spare blade holder



SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-280	18mm	8	6-3/4	179	6	36	076174102802

Retractable Pocket Cutter

- Light-duty, retractable cutter with Quick-Point™ Snap-Off Blades
- Blade sections snap off, providing a fresh, sharp cutting point



SKU #	SIZE	POINTS ON BLADE	LENGTH		BOX QTY	CARTON QTY	UPC
			IN.	MM			
10-143P	18mm	8	6	152	30	180	076174101430

KNIFE AND BLADE SELECTION GUIDE

KNIFE AND BLADE SELECTION GUIDE				FEATURES			BLADES												
				Quick Change	Blade Storage	Clamping	FatMax® 11-700	No. 1992 Drywall 11-937	No. 1991 Paper 11-938	No. 1996 Roofing 11-939	Carton, Rnd Pnt 11-987	Carpet 11-525	Carpet Hvy Dty 11-530	1991® , Reg Dty 11-911	1992®, Hvy Dty 11-921	Extra Hvy Dty 11-931	Safety 11-917	Safety 11-914	Sm Hook 11-961
RETRACTABLE	KNIVES	FatMax Xtreme® 10-789	x	x		x	x	x	x	x			x	x	x			x	x
	FatMax® Retractable 10-778	x	x	x	x	x	x	x	x			x	x	x			x	x	
	InstantChange™ 10-788	x	x		x	x	x	x	x			x	x	x			x	x	
	Dynagrip® 10-779		x			x	x		x			x	x				x	x	
	Quick Change 10-499	x	x			x	x		x			x	x				x	x	
	Swivel-Lock® 10-989	x	x			x	x		x			x	x				x	x	
	Ergonomic All-Metal Retractable Utility Knife 10-707	x	x			x	x		x			x	x				x	x	
	Retractable Utility 10-079		x			x	x		x			x	x				x	x	
	High Visibility 10-179		x			x	x		x			x	x				x	x	
	Classic 99® 10-099		x			x	x		x			x	x				x	x	
	Homeowner's 10-175		x			x	x		x			x	x				x	x	
	Junior Classic Utility Knife 10-016		x			x	x		x			x	x				x	x	
FIXED BLADE	FatMax® Fixed Blade Utility Knife 10-780	x	x	x	x	x	x	x	x			x	x	x			x	x	
	Swivel-Lock® 10-399	x	x			x	x	x	x			x	x	x			x	x	
	Ergonomic All-Metal Fixed Blade Utility Knife 10-705	x	x			x	x	x	x			x	x	x			x	x	
	Classic 199® 10-209		x			x	x	x	x			x	x	x			x	x	
SPECIALTY	299® Fixed Blade Interlock 10-299		x			x	x	x	x			x	x	x			x	x	
	Retractable Carpet Knife 10-525	x	x	x						x	x								
	FatMax® Hook 10-510																		
	Linoleum Flooring Knife 10-509																		
SAFETY	Sport Utility™ Outdoorsman™ 10-804	x				x	x		x			x	x				x	x	
	Self-Retracting Safety 10-189C		x			x	x		x			x	x	x		x	x	x	
POCKET/HOBBY/CRAFT	Folding Safety Knife 10-784														x				
	Folding Fixed Blade Utility Knife 10-855	x				x	x		x			x	x				x	x	
	QuickSlide™ 10-810	x				x	x		x			x	x				x	x	
	QuickSlide2 Knife 10-812	x										x	x						
SNAP-OFF	QuickSlide™ Sport Utility Knife 10-813	x				x	x					x	x				x	x	
	Folding Pocket Knife 10-049				11-040 & 11-041														
	Metal Mitey-Knife® 10-239		x		11-031														
	No. 1 Hobby Knife Light Duty 10-401				11-411														
	FatMax Xtreme® Snap-Off Knife 10-817		x	x	11-325, 11-725, 11-625, H Series														
	FatMax® Snap-Off Knife 9mm 10-475		x	x	11-300, A Series														
	FatMax® Snap-Off Knife 18mm 10-481		x	x	11-301, 11-718, 11-618, L Series														
	FatMax® Snap-Off Knife 25mm 10-486		x	x	11-325, 11-725, 11-625, H Series														
	FatMax® 18mm Snap-Off Knife 10-421				11-301, 11-718, 11-618, L Series														
	25mm Dynagrip® 10-425				11-325, 11-725, 11-625, H Series														
18mm Quick-Point™ 10-151				11-301, 11-718, 11-618, L Series															
9mm Quick-Point™ 10-150				11-300, A Series															
18mm Standard Snap-Off 10-280				11-301, 11-718, 11-618, L Series															
18mm Quick-Point™ Cutter 10-143P				11-301, 11-718, 11-618, L Series															

FatMax® Blades

- Induction-hardened edge offers 75% longer-lasting* blade life
- 20% stronger* blade is heat treated for flexibility
- Blade edge remains 35% sharper*

*Based on average values compared with Stanley® 1992® blades



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-700	3	2-7/16	62	.024	10	100	076174117004
11-700A	100	2-7/16	62	.024	6	36	076174760590
11-700L	50	2-7/16	62	.024	6	36	076174760583
11-700T	10	2-7/16	62	.024	10	100	76174760576

Drywall Utility Blades

- Edge is engineered to easily cut abrasive drywall material
- S3 technology double hardens the blade edge for increased* cutting life
- 100% longer life on average compared to Stanley® 11-921 Heavy-Duty Blade, resulting in far fewer blade changes
- Cuts and scores drywall, ceiling tile, wallboard and similar materials
- "DRYWALL" call-out is laser etched on blade to help prevent mixing with standard blades

*Based on average values compared with Stanley® 1992® blades



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-937	3	2-7/16	62	.024	10	100	076174119374
11-937L	50	2-7/16	62	.024	6	24	076174783513

Paper Blade

- Edge is engineered for precision cuts on wall coverings, borders, paperboard and other light sheet materials
- 50% sharper compared to Stanley's 11-911 Regular-Duty Blade
- "PAPER" call-out is laser etched on blade to help prevent mixing with standard blades



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-938W	3	2-7/16	62	.024	5	25	076174119381


1991® Extra Heavy-Duty Utility Blades

- Cuts thick, dense sheet materials
- Designed for use in fixed blade knives only



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-931	5	2-7/16	62	.035	10	200	076174004939
11-931A	100	2-7/16	62	.035	1	10	076174119312


BLADES



1992® Heavy-Duty Utility Blades

- Engineered for general-purpose cutting
- Precision-honed edge for consistent and long cutting life
- Fits most standard utility knives

SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-921	5	2-7/16	62	.024	10	200	076174119213
11-921A	100	2-7/16	62	.024	4	24	076174119923
11-921B	400	2-7/16	62	.024	1	10	076174114928
11-921G		2-7/16	62	.024	10	60	076174119213
11-921L	50	2-7/16	62	.024	6	24	076174729078
11-921T	10 w/ disp	2-7/16	62	.024	10	100	076174005783
11-921W	10	2-7/16	62	.024	7	42	076174795905



Round-Point Utility Blade

- Rounded edge helps reduce risk of accidental cuts
- Helps prevent damage to carton contents when opening boxes
- Fits most standard utility knives


SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-987	5	1-7/8	48	.024	10	200	076174119879



1991® Regular-Duty Utility Blade

- Regular-duty utility blade for light sheet materials, paper and cardboard
- Fits most standard utility knives

SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-911	5	2	51	.017	10	200	076174119114



Safety Blades

- Edge helps reduce risk of accidental cuts

SKU #	DESCRIPTION	NUMBER OF BLADES	BOX QTY	CARTON QTY	UPC
11-917	For use in 10-784 safety knives	3	20	100	076174119176
11-914	For use in 10-781 and 10-782 safety knives	5	20	100	076174119145



Roofing Utility Blades

- Edge is engineered to withstand the rigors of cutting today's heavy and thick roofing materials
- 75% stronger than Stanley's 11-983 Hook Blade, resulting in fewer blade changes
- Cuts roofing shingles, felt paper, Tyvek®, foam board, insulation, shingles and other building materials
- Designed for use in fixed blade knives only
- "ROOF" call-out is laser etched on blade to help prevent accidental mixing with standard blades



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-939	5	1-7/8	48	.031	10	100	076174119398

Regular Hook Blades

- Edge protection blade for cutting and trimming roofing materials, linoleum, carpet, fabric, cartons and sheet materials
- Blade shape helps prevent damage to whatever is beneath material being cut
- Fits most standard utility knives



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-961	5	2-1/16	53	.024	10	200	076174119619
11-961A	100	2-1/16	53	.024	6	24	076174119961

1996™ Large Hook Blades

- Similar to 11-961, but with deeper hook for cutting thicker materials
- Fits most standard utility knives



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-983	5	1-7/8	48	.024	10	200	076174119831
11-983L	50	1-7/8	48	.024	4	24	076174783506

Tyvek is a registered trademark of E. I. du Pont de Nemours and Company or its affiliates.

BLADES



FatMax® Snap-Off Blades

- 75% longer life*
- 35% sharper*
- 20% stronger*

**Than traditional Stanley Snap-Off Blades*

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-718	18mm	5	8	4-1/4	108	.020	10	50	076174117189
11-718L	18mm	50	8	4-1/4	108	.020	4	24	076174760606
11-718T	18mm	10	8	4-1/4	108	.020	10	50	076174760545
11-725	25mm	5	7	5-1/2	140	.027	6	36	076174117257
11-725L	25mm	50	7	5-1/2	140	.027	2	24	076174760613
11-725T	25mm	10	7	5-1/2	140	.027	4	48	076174760552



Super Heavy-Duty Quick-Point™ Blades

- Replacement blade for the Stanley® 1" Snap-Off Knife (10-425)
- Fits most 25mm snap-off blade knives

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-325	25mm	5	7	5-1/2	140	.027	6	36	076174760385
11-325T	25mm	10	7	5-1/2	140	.027	4	48	076174113259




Quick-Point™ Blades

- Replacement blade with 8 cutting points
- Fits Stanley® 10-218, 10-480, 10-380, 10-280, 10-220, 10-481 and 10-151 Snap-Off Blade Knives and most other 18mm snap-off blade knives

SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-301	18mm	3	8	4-1/4	108	.020	10	50	076174113013
11-301K	18mm		8	4-1/4	108	.020	12	48	076174113013
11-301L	18mm	50	8	4-1/4	108	.020	4	24	076174799231
11-301T	18mm	10	8	4-1/4	108	.020	10	100	076174799248

Snap-Off Hook Blades


- 4 cutting points per blade
- Each snap-off hook blade is equivalent to 2 regular hook blades
- Ideal for cutting asphalt shingles, roofing felt, tar paper



SKU #	SIZE	NUMBER OF BLADES	POINTS ON BLADE	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
				IN.	MM				
11-618	18 mm	5	4	4-1/8	105	.065	10	50	076174116182
11-618L	18mm	20	4	4-1/8	105	.065	5	25	076174760620
11-618T	18mm	10	4	4-1/8	105	.065	10	50	076174760521
11-625	25mm	5	4	5-1/4	132	.065	6	36	076174116250
11-625L	25mm	20	4	5-1/4	132	.065	2	24	076174760637
11-625T	25mm	10	4	5-1/4	132	.065	4	48	076174760538

Mitey-Knife® Blade

- High carbon steel blade
- Fits Stanley® 10-039, 10-139 and 10-239 Mitey-Knife® products



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
11-031	3	1-1/8	29	.017	10	60	076174110319

Sheepfoot Replacement Blade

- Sheepfoot-style blade made of cutlery stainless-steel
- For heavy cutting and carving



SKU #	FITS	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
			IN.	MM				
11-040	10-049 Utility Knife	1	2-9/16	65	.040	10	60	076174110401

Utility Replacement Blade

- Utility blade made from cutlery stainless-steel
- Designed to perform most any cutting job well



SKU #	FITS	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
			IN.	MM				
11-041	10-049 Utility Knife	1	2-9/16	65	.040	10	100	076174110418

Carpet Knife Blades

- High carbon steel blade with double cutting edge
- Fits Stanley® and most other carpet knives
- Five blades per card



SKU #	DESCRIPTION	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
			IN.	MM				
11-525	Standard Carpet Blade	5	2-1/4	55	.015	10	100	076174115253
11-530	Heavy-Duty Carpet Blade	100	2-1/4	55	.017	100	1000	076174115307

Single-Edge Razor Blades

- Steel-backed high carbon steel blade fits most standard razor blade tools
- Replacement blades for Stanley® 28-100 and 28-500 scrapers



SKU #	NUMBER OF BLADES	LENGTH		THICKNESS	BOX QTY	CARTON QTY	UPC
		IN.	MM				
28-510	10	1-1/2	38	.009	10	100	076174285109