


Cable Lug 32/35 mm DIN-Rail Terminals

Feed Through


SS 6




SS 8



SS 10



SS 12



Available Options		Version								
		KrG	0498220000	0649820000	0498100000	1331900000	0484900000	1332000000	0498300000	1332100000
For TS 35 x 7		PA								
For TS 35 x 15/2-3		PA								
Dimensions										
Width / Length / Height mm (in.)	with TS 35 x 7.5	↖	18/49.5/54.5 (.71/1.95/2.15)	36.5/60/68 (1.44/2.36/2.68)		36.5/60/68 (1.44/2.36/2.68)		36.5/60/72 (1.44/2.36/2.84)		
	with TS 32	↗	18/40/62 (.71/1.58/2.44)	36.5/60/68 (1.44/2.36/2.68)		36.5/60/68 (1.44/2.36/2.68)		36.5/60/72 (1.44/2.36/2.84)		
Technical Data										
Rated voltage / rated current / conductor size	UL									
	CSA									
	VDE		400 V* / 76 A / 16 mm²	1500 V* / 125 A / 35 mm²		1000 V* / 192 A / 76 mm²		1000 V* / 232 A / 95 mm²		
Rated voltage / rated current / cross-section										