

# HC-EVO-B10-SHWS-2SSM32-PLRBK

Order No.: 1407636

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407636>

HEAVYCON EVO box mounting base, plastic, B10, with single locking latch, height:74 mm, with gland, 2 x M32, one of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

**Commercial data**

|                        |                 |
|------------------------|-----------------|
| EAN                    | 4 046356 776981 |
| Pack                   | 1               |
| Customs tariff         | 85389099        |
| Gross weight in pieces | 22.22 g         |
| Country of Origin      | PL              |

**Product notes**

WEEE/RoHS-compliant since:  
03/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

**Technical data****General data**

|        |                                                  |
|--------|--------------------------------------------------|
| Note   | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Design | B10                                              |
| Height | 74 mm                                            |
| Width  | 57 mm                                            |

|                                         |                                                                                                         |
|-----------------------------------------|---------------------------------------------------------------------------------------------------------|
| Length                                  | 93 mm                                                                                                   |
| Housing type                            | Box mounting bases                                                                                      |
| Color                                   | black                                                                                                   |
| Locking type                            | With single locking latch                                                                               |
| No. of cable exits                      | 2                                                                                                       |
| Cable exit                              | Lateral                                                                                                 |
| Type of the screw connection            | 2x M32                                                                                                  |
| Protective cover                        | No                                                                                                      |
| Degree of protection for housing        | IP65                                                                                                    |
| Ambient temperature (operation)         | -40 °C ... 125 °C                                                                                       |
| Housing material                        | Polyamide                                                                                               |
| Seal material                           | NBR                                                                                                     |
| Material lock                           | Polyamide                                                                                               |
| Inflammability class according to UL 94 | V0                                                                                                      |
| Connection                              | One of the two openings for the screw connections is sealed but can be broken open using a screwdriver. |

#### Certificates

Certification

Certifications applied for:


Certification Ex:

#### Accessories

| Item           | Designation          | Description                                                                                                           |
|----------------|----------------------|-----------------------------------------------------------------------------------------------------------------------|
| <b>General</b> |                      |                                                                                                                       |
| 1407693        | HC-B10-BC-HI-PLBK    | HEAVYCON EVO hinged protective cover, type B10 for EVO supporting base element, IP65, PA                              |
| 1407698        | HC-B10-SL-PLBK       | Replacement single locking latch for HEAVYCON EVO housing type B10, PA                                                |
| 1407707        | HC-B10-SP-RBK        | Profile gasket for HEAVYCON EVO supporting base element type B10                                                      |
| 1407673        | HC-K-KV-M32(12-21)BK | Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 12 - 21 mm, WAF 36, screw connection: M32 |

**Drawings**

Dimensioned drawing



Dimensional drawing

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;