

Quick Links

- [RoHS/LF P/N Search](#)
- Documentation**
- [Customer drawing search](#)
- [Free search](#)
- Services**
- [Distributor list](#)

Start > Search=60011741* > 60011741

60011741

60011741 : DCS-2 Female 2.8 mm Terminal



Customer drawing

ACTIVE

[Add to Favorites](#)

[Print Datasheet](#)

FCI Brings You More

- [Contact our sales/technical support](#)
- [Sample request](#)

Specifications

[Download document](#)

[Mating Half](#)

General **Dimensional** **Electrical** **Mechanical** **Physical** **Environmental** **Other Features**

General

Product Type	Terminal system
Terminal size (in mm)	2.8
Family	DCS
Features	<p>Suitable for secondary lock</p> <p>Long auxiliary steel spring in CrNi</p> <p>DCS-2</p> <p>Contact beams assisted by the steel spring yield a zero gap</p> <p>Compatible with other terminals</p> <p>Not suitable for mat seal</p>

Dimensional

Wire size range Min - Max	> 1 - 2.5 mm ²
Pitch	5 mm

Electrical

Current Carrying Capacity at 23°C	33A
Current Carrying Capacity at 85°C	22A
Current Carrying Capacity at 100°C	17A
Maximum Insulation (in mm)	3
Resistance (Contact)	< 2 mohms

Mechanical

Contact mating force	< 9N
Single Wire Seal Compatible	No
Contact unmating force	< 5N

Physical

Plating	Sn
Material	CuSn/CrNi

Environmental

IMDS	Yes
------	-----

Other Features

Market	Passenger Vehicles
Type	Female
Crimping Tool	65200402
Tradename	DCS

Disclaimer

Displayed data is for information purposes only.
For more information, please contact your local sales office.
The supply of some products might be limited to some customers.