

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19073-0168](#)
Status: **Active**
Overview: Ring Tongue - Spade Terminals
Description: Avikrimp™ Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 8 (M4), Expanded Flare, Length 27.71mm

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19073](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Ring Tongue - Spade Terminals](#)
Product Name Avikrimp™
Type Ring
UPC 800753076969

Physical


Barrel Type Closed
Flammability 94V-2
Insulation Nylon (PA)
Material - Plating Mating Tin
Net Weight 2.252/g
Packaging Type Bag
Stud Size 8 (M4)
Wire Insulation Diameter 6.35mm max.
Wire Size AWG 10, 12
Wire Size mm² 4.00 - 6.00

Material Info

Old Part Number C-828-08X

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing CCD80105



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19073Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100