







Kabelzuschnitt
Stripping dimension



Fuer Kabel /
For cable

Gr.	Type Typ	ØD1 max.	ØD2 max.	ØD3 max.	ØD4 max.	ØD5	ØD6	ØD7	ØD8	Crimp Aussen/out	
1	RG 178 BU;RG 196 AU;	2,10	1,30	0,90	0,30	1,15	1,70	2,25	3,10	2,67	
2	RG 174 BU;RG 316 U;	2,92	2,20	1,58	0,54	1,60	2,30	3,00	4,00	3,25	
3											
4											
5	RG 316 U-d;	3,10	2,50	1,55	0,54	1,60	2,30	3,35	4,05	3,25	

IMS CONNECTOR
SYSTEMS

general tolerance
ISO 2768
mH

scale: 5:1

Assembly instruction: M8
Stripping dimension: K9

					date	name
186/02	I	Kabelø	12.03.02	I.S.	checked	Zech
149/02	k	UEBERARBEITUNG	04.03.02	I.S.	Norm	
546/01	j	UEBERARBEITUNG	04.08.01	Mayer	30882	
524/98	i	Ueberarbeitung	24.09.98	Fa		
058/98	h	KG1 UEBERARB.	10.02.98	Ma		
		NEUE URZEICHNUNG.				
nr.	rev.	alteration	date	name		



Kabelwinkelstecker

Cable mount angle plug

004.01.1420.0''

Rev.
I

QP TM PA LV SP