

Ball tap wrenches

Version: die-cast zinc housing
Shank: square as per DIN 10

Ideal for rapid fitting of taps.

1.6

Packing unit:
Individual plastic pack

Size	Length mm	for hand tape size			Article no.	Price / each €
		M	Ww	G		
0	200,0	M 1 - M 4	1/16 - 5/32	—	241 200	
1	200,0	M 3,5 - M 8	5/32 - 5/16	—	241 201	
2	240,0	M 4 - M 10	5/32 - 3/8	—	241 202	
3	300,0	M 5 - M 12	7/32 - 1/2	—	241 203	
4	340,0	M 9 - M 12	3/8 - 5/8	—	241 204	
5	450,0	M 12 - M 20	1/2 - 13/16	—	241 205	
6	650,0	M 18 - M 27	1 1/16 - 1	—	241 206	



Die stocks as per DIN 225

Version: die-cast zinc housing

For closed and slotted taps as per DIN EN 24231. With steel handles one of which can be unscrewed and five screws for clamping the tap.

Packing unit:
Individual plastic pack

Size	Thickness mm	Length mm	for tap size			Article no.	Price / each €
			M + MF	Ww	G		
16	5,0	160,0	M 1 - M 2,6	1/16 - 3/32	—	242 165	
20	5,0	200,0	M 3 - M 4	1/8 - 5/32	—	242 205	
20	7,0	200,0	M 4,5 - M 6	3/16 - 1/4	—	242 207	
25	9,0	224,0	M 7 - M 9	5/16	1/16	242 259	
30	11,0	280,0	M 10 - M 11	3/8 - 7/16	1/8	242 3011	
38	10,0	315,0	MF 12 - MF 14	—	1/4	242 3810	
38	14,0	315,0	M 12 - M 14	1/2 - 9/16	—	242 3814	
45	14,0	450,0	MF 16 - MF 20	—	3/8 - 1/2	242 4514	
45	18,0	450,0	M 16 - M 20	5/8 - 3/4	—	242 4518	
55	16,0	560,0	MF 22 - MF 24	—	5/8 - 3/4	242 5516	
55	22,0	560,0	M 22 - M 24	7/8 - 1	—	242 5522	
65	18,0	630,0	MF 27 - MF 36	—	7/8 - 1	242 6518	
65	25,0	630,0	M 27 - M 36	1 1/8 - 1 3/8	—	242 6525	
75	30,0	740,0	M 38 - M 42	1 1/2 - 1 5/8	—	242 7530	
75	20,0	740,0	MF 38 - MF 42	—	1 1/8 - 1 1/4	242 7520	
90	36,0	900,0	M 45 - M 52	1 3/4 - 2	—	242 9036	
90	22,0	900,0	MF 45 - MF 52	—	1 3/8 - 1 5/8	242 9022	
105	36,0	975,0	M 54 - M 63	2 1/4 - 2 3/4	—	242 10536	
105	22,0	975,0	MF 54 - MF 63	—	1 3/4 - 2	242 10522	

