

Olympic P/N 16 MTW, MTW Cable



MTW Cable

TYPE MTW 90°C/TFF 60°C/AWM 105°C/VW-1 600 Volts

Stranded bare Copper, PVC Insulation

- Ratings:**
- **18 & 16 AWG:**
UL 600 Volts, 90°C MTW, 60°C TFF
105°C dry 60°C wet AWM (VW-1)
105°C & 90°C 1000 volts AWM
 - **14, 12 & 10 AWG:**
UL 600 Volts, 90°C MTW, 60°C TW
105°C dry 60°C wet AWM (VW-1)
105°C & 90°C 1000 volts AWM
 - **8 AWG:**
UL 600 Volts, 90°C MTW, 60°C TW
105°C dry 60°C wet, 105°C & 90°C
1000 volts AWM (VW-1)
 - **6, 4 & 2 AWG:**
UL 600 Volts, 90°C MTW, 75°C THW
60°C oil resistant II, 105°C dry 60°C wet
105°C 1000 volts AWM (VW-1)

SPECIFICATIONS

Conductor Size	16 AWG
Stranding	26/.0100 Bare Copper
Insulation	PVC
Nom. Wall Thickness	0.030 in
Nom. O.D.	0.120 in
UL Style	1015 1032 1230 MTW
UL Rating	-20°C to +105°C, 600V, 1000 V
UL Flame Test	VW-1
CSA Type	TEW, TR-32
CSA Flame Test	FT-1

RoHS Compliant



RoHS Compliant