



### Specifications:

1. Rating : 0.3A at 30VDC
2. Contact Resistance : 30 m.  $\Omega$  max at 5VDC1A(Initial)
3. Insulation Resistance : Over 100M.  $\Omega$  500VDC
4. Dielectric Strength : 500VAC for 1 minute
5. Operating Force : 250 $\pm$ 100g
6. Key Travel(Stroke) : 3mm
7. Operating Life : 10000 cycles
8. Solderability : 230 $\pm$ 5..for 3 sec.
9. Soldering Heat Resistance : 250 $\pm$ 5 $\square$ 5 seconds

| 8   | Moving Clip | 2   | BeCuP      | Ag-P       |
|-----|-------------|-----|------------|------------|
| 7   | Spring      | 1   | SWP        | Oil-temper |
| 6   | Base Plate  | 1   | PEM        | t=1.2      |
| 5   | Terminal B  | 4   | BsP        | Ag-P       |
| 4   | Terminal A  | 4   | BsP        | Ag-P       |
| 3   | Ball        |     | Steel ball |            |
| 2   | Knob        | 1   | ABS        | Black      |
| 1   | Frame       | 1   | SPCC       |            |
| No. | Parts Name  | QTY | Material   | Treatment  |

### Slide Switch

P/N

SP-112 (DP3T)