



[Back to Result](#)

PCSB2/0-6S-4Y [Add to BOM](#) | [Add to Favorites](#)

Multi-Tap Connector, single-sided, 6 ports.



Product Details	Related Documents
Std. Ctn. Volume (cf)	0.0000
Std. Pkg. Qty.	4
Std. Pallet Volume (cf)	0.000000
Std. Pallet Weight (lb)	0.0000
Std. Ctn. Weight (lb)	0.0000
RoHS Compliancy Status	Compliant
Note	PCSB2/0-6S-4Y replaces PCSB2/0-6S-4
Part Description	Multi-Tap Connector, single-sided, 6 ports.
Material	Aluminum, Insulated with Clear PVC
CSA Certified	Yes
UL Listed	Yes
Width (mm)	33.3
Width (In.)	1.31
Length (mm)	106.7
Length (In.)	4.20
Height (In.)	1.38
Depth (mm)	106.7
Height (mm)	35.1
Aluminum or Copper Conductor Size Range	2/0 - #14 AWG STR #10 - #14 AWG SOL
Spacing (In.)	0.67
CE Compliant	No
Tightening Torque (In-Lbs)	120
Hex Key Size (In.)	3/16
Pricing Description	Multi-Tap Connector, Single-Sided, Clear Insulation, 6 Ports, 2/0 - #14 STR
Product Type	Multi-Tap Connectors
No. of Ports	6
Min. Order Qty.	1.0000