



10	9	8	7	6	5	4	3	2	19193
MATERIAL NO. LOOSE PIECE	ENG. NO.	MATERIAL NO. TAPE MOUNTED	ENG. NO.	STUD SIZE	±.003 "S"	STOCK THICKNESS			
191930243	E-360-08	191930244	E-360-08T	8	.173	.050/(1.27)			
191930245	E-360-10	191930247	E-360-10T	10	.198				
191930248	E-360-14	191930250	E-360-14T	1/4	.265				
191930251	E-360-56	191930253	E-360-56T	5/16	.328				

(B)



SALES DRAWING

NOTE(S):

1. MATERIAL: COPPER
2. PLATING: ELECTROPLATE TIN
3. ALL DIMENSIONS IN INCHES/(MM).
4. WIRE SIZE: 6 AWG
16 MM²

(B) 5. PART IS ROHS COMPLIANT.

REVISED MATL THKNS EC NO: ETC2007-0011 2006/07/12 DRAWN: EHLE 2006/07/13 CHKD: JMACNEIL 2006/07/17 APPR: RDEROSS B	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 						
				mm	INCH	DRAWN BY DLM	DATE 03/07/28	TITLE RING TONGUE TERMINAL VERSAKRIMP SERIES 6 AWG							
			4 PLACES	± ---	± ---	CHECKED BY HEB	DATE 03/07/28								
			3 PLACES	± ---	± .005	APPROVED BY RWD	DATE 03/07/28	MOLEX INCORPORATED 							
			2 PLACES	± 0.13	± .01	MATERIAL NO. SEE CHART						DOCUMENT NO. SD-19193-032		SHEET NO. 1 OF 1	
			1 PLACE	± 0.25	± ---										
			ANGULAR ±1/2°			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
			REV			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							