



SPECIFICATION

Light output	210   20 lumens
Light source	Cree XR-E Q5 LED
Run time	3h+   24h
Battery	4.8V 2200 mA/h Ni-MH
Charge time	8h
Product size (mm)	L170 x W86 x H177
Product weight (kg)	0.70
Boxed size (mm)	L189 x W187 x H96
Boxed weight (kg)	0.90
Part no.	NSTRIGGER



HIGH PERFORMANCE RECHARGEABLE LED SPOTLIGHT

The **TRIGGER** is the first lightweight LED alternative to 2–3 million candle power halogen searchlights, which are very inefficient compared to the **LED TRIGGER**. The unique deep reflector system combined with high intensity Cree® LED provide a spot beam able to cover vast areas. Using only 210 lumens, it offers 5 times the performance against conventional searchlights.

This spotlight will operate for 3h at full brightness, and will continue to operate for 3h+ at reducing brightness. The **TRIGGER** also offers Low and Strobe light modes.

Compact and lightweight, the **TRIGGER** is ideal for applications requiring high performance and long running times.

- 210 | 20 lumens
- 400 metre spot beam
- Will operate for 3h+
- Compact and lightweight
- 3 light modes: High, low and strobe
- Battery charging indicator
- Easy-use trigger switch and mode selector
- **Supplied with:** Wrist strap, mains charger and vehicle charger
- **Used by:** Security Groups, Search and Rescue, Environmental Agencies and Railways
- **Applications:** Overhead line inspection, Search & Rescue

