






NOTES:

1. MATERIAL: NYLON, UL 94V-2, WHITE
2. FINISH: N/A
3. PRODUCT SPECIFICATION: PS-172160-0001
4. PACKAGING SPECIFICATION: PK-172159-0001
5. COSMETIC SPEC: PS-45499-002 CLASS B
6. HOUSING ACCEPTS TERMINAL: 172159
7. THIS PART WITHOUT THE HOOK SEE SD-172159-0000
8. DIMENSION TO BE 2.54-2.79/.100-.110 TO POLARIZE HOUSING AND PCB.

TERMINAL 172160
SHOWN FOR
REF ONLY



SECTION Z-Z



CKTS	MATERIAL NO	HOOK	POL RIB	DIM A	DIM B	DIM C	DIM E
02	172159-0502	1-2	N/A	$\frac{15.70}{.618}$	$\frac{20.24}{.797}$	$\frac{16.05}{.632}$	$\frac{7.92 \pm 0.05}{.312 \pm .002}$
03	172159-0503	1-2	N/A	$\frac{19.66}{.774}$	$\frac{22.30}{.878}$	$\frac{20.02}{.788}$	$\frac{11.89 \pm 0.05}{.468 \pm .002}$
04	172159-0604	3-4	2-3	$\frac{23.42}{.922}$	$\frac{26.26}{1.034}$	$\frac{23.98}{.944}$	$\frac{15.85 \pm 0.08}{.624 \pm .003}$
05	172159-0605	3-4	2-3	$\frac{27.38}{1.078}$	$\frac{30.23}{1.190}$	$\frac{27.94}{1.100}$	$\frac{19.81 \pm 0.08}{.780 \pm .003}$
06	172159-0606	3-4	2-3	$\frac{31.29}{1.232}$	$\frac{34.19}{1.346}$	$\frac{31.90}{1.256}$	$\frac{23.77 \pm 0.08}{.936 \pm .003}$
07	172159-0607	4-5	3-4	$\frac{35.26}{1.388}$	$\frac{38.15}{1.502}$	$\frac{35.86}{1.412}$	$\frac{27.74 \pm 0.10}{1.092 \pm .004}$
08	172159-0608	4-5	3-4, 6-7	$\frac{39.22}{1.544}$	$\frac{42.11}{1.658}$	$\frac{39.83}{1.568}$	$\frac{31.70 \pm 0.10}{1.248 \pm .004}$
09	172159-0609	4-5	3-4, 5-6	$\frac{43.18}{1.700}$	$\frac{46.08}{1.814}$	$\frac{43.79}{1.724}$	$\frac{35.66 \pm 0.15}{1.404 \pm .006}$
10	172159-0610	4-5	3-4, 6-7	$\frac{47.09}{1.854}$	$\frac{50.04}{1.970}$	$\frac{47.75}{1.880}$	$\frac{39.62 \pm 0.15}{1.560 \pm .006}$
11	172159-0611	4-5	3-4, 7-8	$\frac{51.05}{2.010}$	$\frac{54.00}{2.126}$	$\frac{51.71}{2.036}$	$\frac{43.59 \pm 0.15}{1.716 \pm .006}$
12	172159-0612	5-6	3-4, 8-9	$\frac{54.97}{2.164}$	$\frac{57.96}{2.282}$	$\frac{55.68}{2.192}$	$\frac{47.55 \pm 0.15}{1.872 \pm .006}$

ADD NOTE 8
EC NO: UCP2015-1347
DRAWN: KIPPER 2014/09/29
CHKD: NGUYEN 2014/09/29
APPR: FSMITH 2014/10/10
REV B5

DESCRIPTION

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm .005$	$\pm .0004$
3 PLACES	$\pm .008$	$\pm .0005$
2 PLACES	$\pm .015$	$\pm .0010$
1 PLACE	$\pm .038$	$\pm .0025$
0 PLACE	$\pm .076$	$\pm .0050$

ANGULAR $\pm 1/2^\circ$
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE MM/IN

DRAWN BY	DATE
KSAMIEC	2014/05/05
CHECKED BY	DATE
JCOMERC I	2014/05/19
APPROVED BY	DATE
JCOMERC I	2014/05/19

MATERIAL NO.
SEE CHART
SIZE B

SCALE 3:1

DESIGN UNITS INCH

THIRD ANGLE PROJECTION

EDGEMATE CONNECTOR
3.96/.156 CENTER
WITH HOOK

moLEX

DOCUMENT NO.

SD-172159-0002

SHEET NO.

1 OF 2

