




FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE

NOTES:

1. MADE IN ACCORDANCE WITH PRODUCT SPECIFICATION BUS-12-001 AND PURCHASE SPECIFICATION BUS-10-001.
2. COLOR LIGHT BLUE WITH DARK BLUE TRACER ON EDGE OF FIRST POSITION.
3. UL-LISTED STYLE 2651, CSA CERTIFIED.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family QUICKIE
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
K	-	MRC	4/4/90		angles	.XX±.01/.3	#28 AWG STRANDED DOUBLE SCALLOPED
L	-	MRC	5/29/90		linear	.XXX±.005/.13	PVC ROUND CONDUCTOR CABLE
M	V22247	MSC	6/5/92	0'±2'		.XXXX±.0020/.051	scale 1:1
N	V82042	RGD	11/12/98	dr	M.CORNMAN	4/4/90	dwg no
P	M06-0282	MHT	7/26/06	enr	M.SMYK	4/4/90	sheet 1 of 2
				chr	M.SMYK	4/4/90	size
				appd	M.SMYK	4/4/90	A3
sheet	revision	P	P				type
index	sheet	1	2				Product Customer Drawing

form: A3

PRODUCT NO.
76164-XXX

76164-XXX

NO. OF CONDUCTORS
(MIN. 6, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
6 THRU 15	.007/.18	.010/.25
16 THRU 37	.009/.23	.015/.38
38 THRU 64	.011/.28	.015/.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code		surface ISO 1302 ✓		tolerance ISO 428 ISO 1101		projection 		product family QUICKIE		
ltr	ecn no	dr	date	tolerances unless otherwise specified				title		
P				angles	XXX±.01/.3	INCH/MM		#28 AWG STRANDED DOUBLE SCALLOPED		
				linear	.XXX±.005/.13			PVC ROUND CONDUCTOR CABLE		
				Ø±2°	XXX±.0029/.03	scale 1:1		dwg no		
				dr	M.CORNMANN	4/4/90			sheet2 of 2 size	
				engr	M.SMYK	4/4/90			76164	
				chr	M.SMYK	4/4/90			A3	
				appd	M.SMYK	4/4/90			type Product Customer Drawing	
sheet index		revision sheet								