

**Part Number: 130226-0258***Image not available*

Status: Active - Custom
Series: 130226
Category: Conductor Bars
Old Part Number: AS07

*Series image - Reference only***Product Environmental Compliance**

EU RoHS: Compliance Status Not Reviewed
China RoHS:
REACH SVHC: Not Reviewed
Low-Halogen Status: Not Reviewed

Part Detail**General**

Status	Active - Custom
Category	Conductor Bars
Series	130226
Component Type	Isolation Section Terminal
Current - Max. per Conductor	N/A
Duty	Standard
Product Name	Pow-R-Feed

Physical

Depth	51.40mm
Height	86.25mm
Length	120.00mm
Material - Housing	N/A
Material - Metal	N/A
Material - Resin	ABS
Material - Wheel	N/A
Packaging Type	Individual Carton
Temperature Range - Operating	-30°C TO +60°C

Electrical

(Please review the Product Specification for specific details.)

Voltage - Maximum 600V

Material Info

Old Part Number	AS07
UPC	78678866439

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)