

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

31408-1082

Status:

Active

Overview:

Stac64™ Single, Multi-Pocket and Hybrid Header System

Description:

USCAR 2.54mm Pitch Receptacle, 8 Circuits, Polarization C, Brown

Documents:

3D Model

Drawing (PDF)

Product Specification PS-31408-100 (PDF)

Application Specification AS-34691-100 (PDF)

RoHS Certificate of Compliance (PDF)


General	
Product Family	Crimp Housings
Series	31408
Application	Power, Wire-to-Board
Comments	Polarization C
Overview	Stac64™ Single, Multi-Pocket and Hybrid Header System
Product Name	USCAR
UPC	822348632282

Physical	
Circuits (maximum)	8
Circuits Detail	8
Color - Resin	Brown
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Resin	Modified Polystyrene
Net Weight	3.560/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical	
Current - Maximum per Contact	10.2A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-34691-100
Product Specification	PS-31408-100
Sales Drawing	SD-31408-900



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

31408Series

Mates With

34691 Stac64 Right Angle Assembly. 34690 Stac64 Vertical Assembly

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31408-1082](#)