





FOR 2 & 3 CKTS.



LEGEND

SD-35362-****
CKT NO. _____ COLOR _____

FINAL GOOD (BULK) 5 : SELECTIVE KINK (LEAD FREE)
6 : NONE KINK (LEAD FREE)

SUB ASSY (TUBE) 7 : SELECTIVE KINK (LEAD FREE)
8 : NONE KINK (LEAD FREE)

0 : NATURAL
1 : BLACK
2 : RED
3 : YELLOW
4 : BLUE
5 : GREEN
6 : TUBE PACKING (Natural Color)
7 : TUBE PACKING (Red Color)
8 : TUBE PACKING (Blue Color)






NOTES

- MATERIAL : UNFILLED POLYAMIDE, UL94V-0
PIN : BRASS, TIN PLATED
- FINISHES : PIN : Sn 3-54m OVERALL
- PRODUCT SPECIFICATION : PS-35507-003
- MATING HOUSING : 35507-***0*
MATING TERMINAL : 50212-8000
- KINK

CKT NO	1	2	3
2 CKT			
3 CKT	A	B	A

6. 35362-0287 IS ONLY KINKED 2P

CKT NO	1	2
PRODUCT NO.		
35362-0287	A	B



LEAD FREE	
30 over	±0.3
10 over 30 under	±0.25
10 under	±0.2
ANGLE	±3°
GENERAL TOLERANCE	

REVISED
EC NO: KOR2014-0116
DRW: NTKIM01
CHKD: CHYKD
APPR: YSKIM02
REV

7.3	4	9.7	3536203**	35362-03**	3
5.3	2	7.7	3536202**	35362-02**	2
(C)	B	(A)	MATERIAL NO.	ENG. NO.	CKT

QUALITY SYMBOLS
F=0
F=0
F=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
0 PLACE	±	±

ANGULAR ±---°
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY YSOOKIM
DATE 1996/09/11

CHECKED BY JKOH
DATE 1996/09/11

APPROVED BY _____
DATE _____

MATERIAL NO. _____
SEE TABLE

SCALE 5:1
DESIGN UNITS METRIC

THIRD ANGLE PROJECTION

2.0 W/B WAFER ASS'Y
-LEAD FREE-

molex

DOCUMENT NO. SD-35362-002
SHEET NO. 2 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

10

9

8

7

6

5

4

3

2

1


560±1





ANTISTATIC



6.5



ISOMETRIC VIEW



KINK TABLE(FOR 35362-****)


CKT NO	1	2	3	4	5	N-2	N-1	N
6 CKT OVER	—	A	B	—	—	B	A	—
5 CKT	A	B	—	B	A			
4 CKT	A	B	B	A				
3 CKT	A	B	A					
2 CKT	None Kink							

** 35362-0287 IS ONLY KINKED 2P

CKT NO	1	2
PRODUCT NO.		
35362-0287	A	B

LEAD FREE


LEGEND.



NOTES

1. MATERIAL : TUBE - TRANSLUCENT P.V.C (P-1000)
Wafer - POLYAMIDE, UL94V-0
PIN - BRASS SQ 0.5mm
2. BOW(CAMBER): 1.0mm MAX/Total Length
3. DIMENSIONS GIVEN ACROSS CENTER LINES ARE SYMMETRICAL ABOUT THOSE CENTER LINES WITH HALF THE TOTAL LENGTH.
4. TOTAL TUBE LENGTH : 560mm ± 1mm
5. TWIST : 5° MAX./Total Length
6. BURRS : 0.2mm MAX.
7. SKEW : PRODUCTS MUST BE FLOWED SMOOTHLY WHEN THIS STICK IS PLACES 30° ANGLE.
8. THICKNESS : 0.6mm ± 0.1mm
9. ARTWORK : PER E-35900-0434 (SILK SCREEN COLOR : RED)
10. APPLICABLE STOPPER(RUBBER) : 35900-0435

TABLE



10		20**	-20**	20
10		19**	-19**	19
10		18**	-18**	18
10		17**	-17**	17
15		16**	-16**	16
15		15**	-15**	15
15		14**	-14**	14
15		13**	-13**	13
15		12**	-12**	12
20		11**	-11**	11
20		10**	-10**	10
25		09**	-09**	9
25		08**	-08**	8
30		07**	-07**	7
35		06**	-06**	6
40		05**	-05**	5
50		04**	-04**	4
60		03**	-03**	3
70	3536202**	35362-02**		2
QT'y	Material NO.	ENG. NO.		CKT



REVISED
EC NO: KOR2014-0116
DRW/TKI/M01 2014/04/14
CHKD:
APPR: YSK/M02 2014/04/21

QUALITY SYMBOLS
F_A=0
F_B=0
F_C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± 0.2	± ---
0 PLACE	± ---	±

ANGULAR ± 1 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY YS00KIM DATE 2000/12/11

CHECKED BY JKOH DATE 2000/12/11

APPROVED BY DATE

MATERIAL NO. 9999999999

SIZE A3

SCALE 5:1

DESIGN UNITS METRIC

THIRD ANGLE PROJECTION

TITLE

2.0 W/B WAFER ASS'Y
TUBE PACKING
-LEAD FREE-

molex

DOCUMENT NO. SD-35362-003

SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

9

8

7

6

5

4

3

2

1