



- Durable nylon cable clamps

Part Number:	CCS12-S8-C
Product Family:	Fixed Diameter Cable Clamps
Product Line:	Screw/Rivet Applied

RoHS Compliancy Status:	Compliant
-------------------------	-----------

Part Description:	Fixed Diameter Cable Clamp
-------------------	----------------------------

Product Type:	Mounting Device
---------------	-----------------

Material:	Nylon 6.6
-----------	-----------

Color:	Natural
--------	---------

UL Recognized:	E136577
----------------	---------

Diameter (In.):	.17
-----------------	-----

Diameter (mm):	4.2
----------------	-----

Width (In.):	.37
--------------	-----

Width (mm):	9.4
-------------	-----

Bundle Offset (mm):	8.4
Bundle Offset (In.):	.33
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.17
Hole Diameter (mm):	4.2
Max. Bundle Diameter (In.):	.12
Max. Bundle Diameter (mm):	3.1
Metric Screw Size:	M4
Mounting Method:	#8 (M4) Screw
Screw Size:	#8 (M4)
Std. Pkg. UOM:	PK
Type Of Application:	Standard
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100