


**Part Number: 78028-1104**

1.00mm Pitch, PCI Express* Connector, Press-fit, 0.76µm Gold Tail Length, with Plastic Pegs, 4 Lanes, 64 Circuits, Lead-Free



Series image - Reference only

Status:	OBsolete
Replacement:	Contact Molex
Series:	78028
Category:	Edge Card Connectors

Mates With Part(s):

PCI Express Card

Product Environmental ComplianceEU RoHS: ELV and RoHS Compliant China RoHS: REACH SVHC: Contains SVHC: NoLow-Halogen Status: Not Low-Halogen**Part Detail****General**

Status	Obsolete
Category	Edge Card Connectors
Series	78028
Comments	PCI 4 lanes
Component Type	Edgecard to PCB
Product Name	PCI Express*

Physical

(p)ower-(s)ignal Configuration	64s - 0p
Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
PC Tail Length	3.43mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.18mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.381µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1.1A
Voltage - Maximum	50V AC (RMS)/DC

Material Info**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application
Tooling**
[Check our list of old tooling that used to be
available for this part](#)