

ALL MATERIAL ARE RoHS AND CALIFORNIA PROP.65 COMPLIANT



CUSTOMER'S APPROVAL: _____


DATE: _____

NO. _____

YES, ☐

FIRST ARTICLE SAMPLE REQUIRED: ☐

VDC LOGO (TWO SIDES)



1000±50



Farnell Code 1956245 - 2m; 1956246 - 3m; 1956247 - 6m;
1956295 - 15m; 1956248 - 20m; 1956249 - 30m; 1956250 - 50m

PINOUT CONFIGURATION

HD15 (90°)	
MALE	FEMALE
1	Red Video
2	Green Video
3	Blue Video
4	Ground
5	Red Ground
6	Green Ground
7	Blue Ground
8	+5 VDC
9	
10	
11	
12	DDC Serial Data Line
13	Horizontal Sync (or Composite Sync)
14	Vertical Sync
15	DDC Data Clock Line
SHELL	DRAIN+BRAID
	SHELL

WIRE MARKING:

VDC LONDON WWW.VDCTRADING.COM
E193793 RU AWM 2919 80°C 30V VW-1

UNIT: mm

ITEM	DESCRIPTION	QTY.	UNIT
1	HD15 MALE CONNECTOR	1	PCS.
2	HD15 FEMALE CONNECTOR	1	PCS.
3	PANTONE BLUE 072U MOLDED PVC HOOD W/VDC LOGO (90°)	1	PCS.
4	PANTONE BLUE 072U MOLDED PVC HOOD W/VDC LOGO	1	PCS.
5	PANTONE BLUE 072U #4/40 THUMBSCREW	1	PCS.
6	BLUE #4/40 THUMBSCREW	2	PCS.
7	PAT. NO.:US 6,287,148 B1 RF-BLOK™ SHIELDING METAL CAN	1	PCS.
8	UL2919 (28AWG COAX+AL-FOIL+65%BRAID+INNER JACKET)x3C SEE DWG.	SEE	DWG.
	+(28AWG WIRE)x8C+AL-FOIL+DRAIN+BRAID OVERALL;		
	PANTONE BLUE 072U PVC JACKET		