

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0982660417

Status:


Active

Overview:

Premo-Flex Cable Jumpers

Description:

0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 203.00mm Cable Length, Tin (Sn) Plating, 38 Circuits



Documents:

Drawing (PDF)

Product Specification PS-98266-001-001 (PDF)

Packaging Specification PK-98266-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	98266
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	756054768747
Physical	
Cable Length	203.00mm
Circuits (Loaded)	38
Material - Plating Mating	Tin
Net Weight	2.482/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

98266 Series

Mates With

Easy-On FFC/FPC Connector:

541043833 , 541323833

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION