

The Globe Motors commercial cooling fan product line provides cooling solutions for industrial applications from office copiers, micro-computers and laboratory instrumentation to industrial control cabinets.


Through the use of CAD/CAM and strict statistical process controls (SPC), our fans have a life expectancy of 60,000 hours

and a 0.005% field failure rate (50 parts per million).

Special care has been taken to design-in long operating life and low acoustical noise. All fans use precision, life-lubricated ball bearings.

3

AC Cooling Fans



Dimensions — Inches (mm): 2.36 sq. × 1.18 (60 sq. × 30)

Stock No.	Mfr.'s Type	Nominal Voltage VAC	Acoustic Noise dBA	RPM	CFM	EACH
965-0100	A24-B12A-15W3-000	115	28/29	2350/2900	8/10	20.81

Dimensions — Inches (mm): 3.15 sq. × 1.00 (80 sq. × 25)

965-0105	A31-B10A-15W3-000	115	37/40	2700/3250	17/20	20.81
----------	-------------------	-----	-------	-----------	-------	-------

Dimensions — Inches (mm): 3.15 sq. × 1.50 (80 sq. × 38) on all models

965-0110	A31-B15A-15T1-000	115	23/25	1750/2050	18/21	17.90
965-0115	A31-B15A-15T2-000	115	27/31	2200/2500	21/25	17.90
965-0120	A31-B15A-15T3-000	115	33/38	2750/3250	28/33	17.90
965-0125	A31-B15A-15W1-000	115	23/25	1750/2050	18/21	17.90
965-0130	A31-B15A-15W2-000	115	27/31	2200/2500	21/25	17.90
965-0135	A31-B15A-15W3-000	115	33/38	2750/3250	28/33	17.90
965-0140	A31-B15A-23W1-000	230	23/26	1900/2300	19/24	20.81
965-0145	A31-B15A-23W2-000	230	29/34	2300/2700	22/27	19.41
965-0150	A31-B15A-23W3-000	230	33/38	2750/3300	27/33	19.41

Dimensions — Inches (mm): 3.64 sq. × 1.00 (92 sq. × 25) on all models

965-0155	A36-B10A-15T1-000	115	22/25	1600/2000	18/23	21.35
965-0160	A36-B10A-15T2-000	115	30/35	2300/2700	25/30	21.35
965-0165	A36-B10A-15T3-000	115	33/38	2650/3200	29/36	21.35
965-0170	A36-B10A-23T1-000	230	22/26	1700/2250	20/25	21.35
965-0175	A36-B10A-23T2-000	230	30/35	2300/2700	25/30	21.35
965-0180	A36-B10A-23T3-000	230	34/39	2650/3200	30/36	21.35

Dimensions — Inches (mm): 4.69 sq. × 1.00 (119 sq. × 25) on all models

965-0185	A47-B10A-15T2-000	115	29/30	2050/2250	52/57	21.56
965-0190	A47-B10A-15T3-000	115	34/38	2550/2950	68/77	21.56
965-0195	A47-B10A-23T2-000	230	29/30	2050/2300	52/58	21.56
965-0200	A47-B10A-23T3-000	230	34/38	2500/2850	65/74	21.56

Dimensions — Inches (mm): 4.69 sq. × 1.50 (119 sq. × 38) on all models


965-0205	A47-B15A-15T1-000	115	28/28	1650/1650	53/53	20.27
965-0210	A47-B15A-15T2-000	115	40/43	2600/2900	85/95	20.27
965-0215	A47-B15A-15T3-000	115	42/46	2750/3200	90/105	20.27
965-0220	A47-B15A-23T1-000	230	28/28	1770/1770	58/58	20.27
965-0225	A47-B15A-23T2-000	230	40/43	2600/2850	85/95	20.27
965-0230	A47-B15A-23T3-000	230	43/47	2750/3150	90/105	21.56

Dimensions — Inches (mm): 5.91 sq. × 6.78 × 1.50 Deep (150 sq. × 172 × 38) on all models

965-0235	A59-B15A-15T1-000*	115	35/38	1450/1720	86/105	59.52
965-0240	A59-B15A-15T2-000*	115	46/50	2360/2750	144/170	59.52
965-0245	A59-B15A-15T3-000*	115	52/56	2800/3370	178/215	59.52
965-0250	A59-B15A-23T1-000*	230	35/38	1450/1600	86/105	59.52
965-0255	A59-B15A-23T2-000*	230	46/50	2420/2800	144/170	59.52
965-0260	A59-B15A-23T3-000*	230	52/56	2870/3400	178/215	59.52

W=Lead wires, T=Terminals. *Note Built-In Capacitor Values: 115 VAC Series — 3.0 mF at 250 VAC; 230 VAC Series — 1.0 mF at 350 VAC.

DC Cooling Fans



Dimensions — Inches (mm): 1.60 sq. × 0.60 (40 sq. × 15) on all models

Stock No.	Mfr.'s Type	Nominal Voltage VDC	Acoustic Noise dBA	RPM	CFM	EACH
965-1600	D16-B06A-04W3-000	12	28	5500	6	17.04
965-1602	D16-B06A-04W5-000	12	34	7500	8	17.04

Dimensions — Inches (mm): 2.36 sq. × 0.79 (60 sq. × 20) on all models

965-0265	D24-B08A-04W3-000	12	22	3000	11	21.24
965-0270	D24-B08A-04W4-000	12	26	3800	14	21.24
965-0275	D24-B08A-05W3-000	24	22	3000	11	21.24
965-0280	D24-B08A-05W4-000	24	26	3800	14	21.24

Dimensions — Inches (mm): 2.36 sq. × 1.00 (60 sq. × 25) on all models

965-0286	D24-B10A-04W3-100	12	28	3600	17	17.04
965-0291	D24-B10A-04W4-100	12	33	4600	21	17.04
965-0296	D24-B10A-05W3-100	24	28	3600	17	17.04
965-0301	D24-B10A-05W4-100	24	33	4600	21	17.04

Dimensions — Inches (mm): 3.15 sq. × 1.00 (80 sq. × 25) on all models

965-0311	D31-B10A-04W2-100	12	25	2400	28	18.11
965-0316	D31-B10A-04W3-100	12	28	2700	32	18.11
965-0321	D31-B10A-05W2-100	24	25	2400	28	18.11
965-0326	D31-B10A-05W3-100	24	28	2700	32	18.11

Dimensions — Inches (mm): 3.62 sq. × 1.00 (92 sq. × 25) on all models

965-0351	D36-B10A-04W2-100	12	27	2100	34	19.08
965-0356	D36-B10A-04W3-100	12	28	2850	48	19.08
965-0341	D36-B10A-05W2-100	24	27	2100	34	19.08
965-0346	D36-B10A-05W3-100	24	37	2850	48	19.08

Dimensions — Inches (mm): 4.69 sq. × 1.00 (119 sq. × 25) on all models*

965-0350	D47-B10A-04W2-000	12	34	1900	70	21.56
965-0355	D47-B10A-04W3-000	12	39	2400	90	21.56
965-0360	D47-B10A-05W2-000	24	34	1900	70	21.56
965-0365	D47-B10A-05W3-000	24	39	2400	90	21.56

Dimensions — Inches (mm): 4.69 sq. × 1.50 (119 sq. × 38) on all models

965-0410	D47-B15A-04T2-100	12	40	2650	97	22.64
965-0412	D47-B15A-04T3-100	12	42	2950	108	22.64
965-0414	D47-B15A-05T2-100	24	40	2650	97	22.64
965-0416	D47-B15A-05T3-100	24	42	2950	108	22.64
965-0418	D47-B15A-04W2-100	12	40	2650	97	22.64
965-0420	D47-B15A-04W3-100	12	42	2950	108	22.64
965-0422	D47-B15A-05W2-100	24	40	2650	97	22.64
965-0424	D47-B15A-05W3-100	24	42	2950	108	22.64

Dimensions — Inches (mm): 5.91 × 6.8 × 2 (150 × 172.7 × 50.8) on all models

965-0500	D59-B20A-04W4-000	12	54	3200	230	71.38
965-0510	D59-B20A-05W4-000	24	54	3200	230	71.38
965-0520	D59-B20A-07W4-000	48	54	3200	230	71.38

Dimensions — Inches (mm): 6.8 × 2 (172.7 × 50.8) on all models

965-0600	D68-B20A-04W4-000	12	54	3200	230	71.38
965-0610	D68-B20A-05W4-000	24	54	3200	230	71.38
965-0620	D68-B20A-07W4-000	48	54	3200	230	56.27

*Also available in terminal version.

Accessories

Stock No.	Mfr.'s Type	Description	For Globe Fan Series	EACH	
				1-49	50-Up
965-0012	FPC12	12" Power Cord/45° Connector	All	1.62	1.54
965-2444	FPC24	24" Power Cord/45° Connector	All	1.77	1.68
965-2446	FPC36	36" Power Cord/45° Connector	All	2.05	1.95
965-1012	RPC12	12" Power Cord/90° Connector	All	1.62	1.54
965-9924	RPC24	24" Power Cord/90° Connector	All	1.77	1.68
965-0112	SPC12	12" Power Cord/Straight Connector	All	1.62	1.54
965-0124	SPC24	24" Power Cord/Straight Connector	All	1.77	1.68
965-0212	TPC12	12" Power Cord/T-Head Connector	All	1.62	1.54
965-0224	TPC24	24" Power Cord/T-Head Connector	All	1.77	1.68
965-2428	PFA4730	30 PPI Filter	A47/D47	3.39	3.22

Stock No.	Mfr.'s Type	Description	For Globe Fan Series	EACH	
				1-49	50-Up
965-2445	PFA2445	45 PPI Filter	A24/D24	2.93	2.79
965-2424	PFA3630	30 PPI Filter	A36/D36	3.17	3.01
965-2434	PFG47	Black Plastic Finger Guard	4.69" Sq. Fan	2.11	2.01
965-2432	PFG36	Black Plastic Finger Guard	3.60" Sq. Fan	1.90	1.80
965-0031	PFG31	Black Plastic Finger Guard	3.15" Sq. Fan	1.62	1.54
965-2406	WFG47	Nickel Chrome Finger Guard	4.69" Sq. Fan	2.33	2.21
965-2400	WFG24	Nickel Chrome Finger Guard	2.36" Sq. Fan	1.83	1.74
965-2402	WFG31	Nickel Chrome Finger Guard	3.15" Sq. Fan	1.99	1.89
965-2414	WFG59	Nickel Chrome Finger Guard	5.91" × 6.78" Fan	3.95	3.75
—	—	—	—	—	—

90 ◀ ALLIED

For Local Personalized Service Call 1-800-433-5700