





NOTE:

1. MATERIAL:

HOUSING: PA46 GLASS FILLED, UL94V-0, COLOR: NATURAL

TERMINAL: PHOSPHOR BRONZE

2. PLATING: 1) PARTIAL GOLD PLATING OVER NICKEL PLATING OVERALL

CONTACT POINT: 0.10 μm MINIMUM GOLD PLATING



TAIL POINT :GOLD PLATING

2) 1-3 μm TIN-BISMUTH OVER NICKEL PLATING OVERALL

3. PRODUCT SPECIFICATION: PS-78119-001

4. PRODUCT ARE PACKED IN TAPE & REEL.

REVISED EC NO: J2013-1512 DRW: KAWASHI 101 CHKD: KATAHASHI APPR: YNOGAWA	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
				mm	INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT						
			4 PLACES	± ---	± ---	CHECKED BY BOKOK	DATE 2006/04/18							
			3 PLACES	± ---	± ---	APPROVED BY PTL IM		DATE 2006/04/18		molex				
			2 PLACES	± 0.15	± ---									
			1 PLACE	± ---	± ---									
			0 PLACE	±	±	MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-78119-001				1 OF 7		
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								



N	0.30 ^{+0.05} _{-0.02}	0.30 ^{+0.05} _{-0.02}	0.35 ^{+0.04} _{-0.03}	0.35 ^{+0.05} ₀
P	0.50±0.03	0.50±0.05	0.50±0.02	0.50±0.05
M	0.50±0.10	0.50±0.08	0.50±0.12	0.50±0.10
B	B±0.03	B±0.05	B±0.03	B±0.05
	1	2	1	2
	FFC		FPC	

REVISED EC NO: J2013-1512 DRWN: KAWASHI 101 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/25	QUALITY SYMBOLS	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
						MM ONLY		NTS	METRIC					
				F _A =0 F _G =0 F _P =0		mm	INCH	DRAWN BY	DATE	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT				
					4 PLACES	± ---	± ---	YLQIAO	2006/04/11					
					3 PLACES	± ---	± ---	CHECKED BY	DATE	molex				
					2 PLACES	± 0.15	± ---	BOKOK	2006/04/18					
					1 PLACE	± ---	± ---	APPROVED BY	DATE					
				0 PLACE	±	±	PTLIM	2006/04/18						
				ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78119-001		2 OF 7				
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

10

9

8

7

6

5

4

3

2

1

ELV & RoHS COMPLIANT

TIN-BISMUTH PLATING TERMINAL ASSEMBLY PART NUMBERS

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0109	10	7.10	4.50	6.40	5.60	2
78119-0119	11	7.60	5.00	6.90	6.10	
78119-0129	12	8.10	5.50	7.40	6.60	
78119-0139	13	8.60	6.00	7.90	7.10	
78119-0149	14	9.10	6.50	8.40	7.60	
78119-0159	15	9.60	7.00	8.90	8.10	
78119-0169	16	10.10	7.50	9.40	8.60	
78119-0179	17	10.60	8.00	9.90	9.10	
78119-0189	18	11.10	8.50	10.40	9.60	
78119-0199	19	11.60	9.00	10.90	10.10	
78119-0209	20	12.10	9.50	11.40	10.60	
78119-0219	21	12.60	10.00	11.90	11.10	
78119-0229	22	13.10	10.50	12.40	11.60	
78119-0239	23	13.60	11.00	12.90	12.10	
78119-0249	24	14.10	11.50	13.40	12.60	
78119-0259	25	14.60	12.00	13.90	13.10	
78119-0269	26	15.10	12.50	14.40	13.60	
78119-0279	27	15.60	13.00	14.90	14.10	
78119-0289	28	16.10	13.50	15.40	14.60	
78119-0299	29	16.60	14.00	15.90	15.10	
78119-0309	30	17.10	14.50	16.40	15.60	

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0319	31	17.60	15.00	16.90	16.10	2
78119-0329	32	18.10	15.50	17.40	16.60	
78119-0339	33	18.60	16.00	17.90	17.10	
78119-0349	34	19.10	16.50	18.40	17.60	
78119-0359	35	19.60	17.00	18.90	18.10	
78119-0369	36	20.10	17.50	19.40	18.60	
78119-0379	37	20.60	18.00	19.90	19.10	
78119-0389	38	21.10	18.50	20.40	19.60	
78119-0399	39	21.60	19.00	20.90	20.10	
78119-0409	40	22.10	19.50	21.40	20.60	

REVISED EC NO: J2013-1512 DRWN:AYOSHI I01 CHKD:K TAKAHASHI APPR:YNOGAWA 2013/06/12 2013/06/12 2013/06/25	DESCRIPTION	QUALITY SYMBOLS ▽_A=0 ▽_C=0 ▽_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT		
			4 PLACES	± ---	± ---	CHECKED BY BOKOK	DATE 2006/04/18			
			3 PLACES	± ---	± ---	APPROVED BY PTL IM	DATE 2006/04/18			
			2 PLACES	± 0.15	± ---	molex				
			1 PLACE	± ---	± ---					
			0 PLACE	±	±	MATERIAL NO.	DOCUMENT NO.	SHEET NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-78119-001		4 OF 7
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

9

8

7

6

5



4

3

2

1



EMBOSSED TYPE A

CUSTOMER
PULL OUT DIRECTION

REEL

NOTES:



1. LEADER AND TRAILER TAPE

2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)

3. PACKAGING STANDARD IS AS PER EIA-481.


4. TAPE & REEL QUANTITY = 1000 PCS/REEL

SECTION Y-Y




DETAIL 1

EMBOSSED TYPE B



DETAIL 1



SECTION Z-Z

REVISED EC NO: J2013-1512 DRWN:AYOSHI/01 CHKD:K TAKAHASHI APPR: YNOGAWA REV A4	DESCRIPTION 2013/06/12 2013/06/12 2013/06/25	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
					DRAWN BY YUQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT						
			4 PLACES	± ---	± ---	CHECKED BY BOKOK						DATE 2006/04/18	
			3 PLACES	± ---	± ---	APPROVED BY PTL IM		DATE 2006/04/18	molex				
			2 PLACES	± 0.15	± ---								
			1 PLACE	± ---	± ---								
			0 PLACE	±	±	MATERIAL NO.		DOCUMENT NO.			SHEET NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE			SD-78119-001			5 OF 7	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																														
											ELV & RoHS COMPLIANT																																																																																																																																																																																																																																																																													
F											F																																																																																																																																																																																																																																																																													
E	PARTIAL GOLD PLATING TERMINAL ASSEMBLY PART NUMBERS										E																																																																																																																																																																																																																																																																													
D	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1108</td><td>78119-0108</td><td>10</td><td>24.00</td><td>-</td><td>11.50</td><td>7.40</td><td>5.10</td><td rowspan="10">A</td></tr><tr><td>78119-1118</td><td>78119-0118</td><td>11</td><td>24.00</td><td>-</td><td>11.50</td><td>7.90</td><td>5.60</td></tr><tr><td>78119-1128</td><td>78119-0128</td><td>12</td><td>24.00</td><td>-</td><td>11.50</td><td>8.40</td><td>6.10</td></tr><tr><td>78119-1138</td><td>78119-0138</td><td>13</td><td>24.00</td><td>-</td><td>11.50</td><td>8.90</td><td>6.60</td></tr><tr><td>78119-1148</td><td>78119-0148</td><td>14</td><td>24.00</td><td>-</td><td>11.50</td><td>9.40</td><td>7.10</td></tr><tr><td>78119-1158</td><td>78119-0158</td><td>15</td><td>24.00</td><td>-</td><td>11.50</td><td>9.90</td><td>7.60</td></tr><tr><td>78119-1168</td><td>78119-0168</td><td>16</td><td>24.00</td><td>-</td><td>11.50</td><td>10.40</td><td>8.10</td></tr><tr><td>78119-1178</td><td>78119-0178</td><td>17</td><td>24.00</td><td>-</td><td>11.50</td><td>10.90</td><td>8.60</td></tr><tr><td>78119-1188</td><td>78119-0188</td><td>18</td><td>24.00</td><td>-</td><td>11.50</td><td>11.40</td><td>9.10</td></tr><tr><td>78119-1198</td><td>78119-0198</td><td>19</td><td>24.00</td><td>-</td><td>11.50</td><td>11.90</td><td>9.60</td></tr><tr><td>78119-1208</td><td>78119-0208</td><td>20</td><td>24.00</td><td>-</td><td>11.50</td><td>12.40</td><td>10.10</td><td rowspan="10">B</td></tr><tr><td>78119-1218</td><td>78119-0218</td><td>21</td><td>32.00</td><td>28.40</td><td>14.20</td><td>12.90</td><td>10.60</td></tr><tr><td>78119-1228</td><td>78119-0228</td><td>22</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.40</td><td>11.10</td></tr><tr><td>78119-1238</td><td>78119-0238</td><td>23</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.90</td><td>11.60</td></tr><tr><td>78119-1248</td><td>78119-0248</td><td>24</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.40</td><td>12.10</td></tr><tr><td>78119-1258</td><td>78119-0258</td><td>25</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.90</td><td>12.60</td></tr><tr><td>78119-1268</td><td>78119-0268</td><td>26</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.40</td><td>13.10</td></tr><tr><td>78119-1278</td><td>78119-0278</td><td>27</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.90</td><td>13.60</td></tr><tr><td>78119-1288</td><td>78119-0288</td><td>28</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.40</td><td>14.10</td></tr><tr><td>78119-1298</td><td>78119-0298</td><td>29</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.90</td><td>14.60</td></tr><tr><td>78119-1308</td><td>78119-0308</td><td>30</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.40</td><td>15.10</td></tr></table>								ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A	78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60	78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10	78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60	78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10	78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60	78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10	78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60	78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10	78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60	78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B	78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60	78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10	78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60	78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10	78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60	78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10	78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60	78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10	78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60	78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1318</td><td>78119-0318</td><td>31</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.90</td><td>15.60</td><td rowspan="10">B</td></tr><tr><td>78119-1328</td><td>78119-0328</td><td>32</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.40</td><td>16.10</td></tr><tr><td>78119-1338</td><td>78119-0338</td><td>33</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.90</td><td>16.60</td></tr><tr><td>78119-1348</td><td>78119-0348</td><td>34</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.40</td><td>17.10</td></tr><tr><td>78119-1358</td><td>78119-0358</td><td>35</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.90</td><td>17.60</td></tr><tr><td>78119-1368</td><td>78119-0368</td><td>36</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.40</td><td>18.10</td></tr><tr><td>78119-1378</td><td>78119-0378</td><td>37</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.90</td><td>18.60</td></tr><tr><td>78119-1388</td><td>78119-0388</td><td>38</td><td>32.00</td><td>28.40</td><td>14.20</td><td>21.40</td><td>19.10</td></tr><tr><td>78119-1398</td><td>78119-0398</td><td>39</td><td>44.00</td><td>40.40</td><td>20.20</td><td>21.90</td><td>19.60</td></tr><tr><td>78119-1408</td><td>78119-0408</td><td>40</td><td>44.00</td><td>40.40</td><td>20.20</td><td>22.40</td><td>20.10</td></tr></table>		ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B	78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10	78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60	78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10	78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60	78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10	78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60	78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10	78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60	78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10	D
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																
78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A																																																																																																																																																																																																																																																																																
78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60																																																																																																																																																																																																																																																																																	
78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10																																																																																																																																																																																																																																																																																	
78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60																																																																																																																																																																																																																																																																																	
78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10																																																																																																																																																																																																																																																																																	
78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60																																																																																																																																																																																																																																																																																	
78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10																																																																																																																																																																																																																																																																																	
78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60																																																																																																																																																																																																																																																																																	
78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10																																																																																																																																																																																																																																																																																	
78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60																																																																																																																																																																																																																																																																																	
78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B																																																																																																																																																																																																																																																																																
78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60																																																																																																																																																																																																																																																																																	
78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10																																																																																																																																																																																																																																																																																	
78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60																																																																																																																																																																																																																																																																																	
78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10																																																																																																																																																																																																																																																																																	
78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60																																																																																																																																																																																																																																																																																	
78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10																																																																																																																																																																																																																																																																																	
78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60																																																																																																																																																																																																																																																																																	
78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10																																																																																																																																																																																																																																																																																	
78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60																																																																																																																																																																																																																																																																																	
78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10																																																																																																																																																																																																																																																																																	
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																																
78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B																																																																																																																																																																																																																																																																																
78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10																																																																																																																																																																																																																																																																																	
78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60																																																																																																																																																																																																																																																																																	
78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10																																																																																																																																																																																																																																																																																	
78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60																																																																																																																																																																																																																																																																																	
78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10																																																																																																																																																																																																																																																																																	
78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60																																																																																																																																																																																																																																																																																	
78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10																																																																																																																																																																																																																																																																																	
78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60																																																																																																																																																																																																																																																																																	
78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10																																																																																																																																																																																																																																																																																	
C											C																																																																																																																																																																																																																																																																													
B											B																																																																																																																																																																																																																																																																													
A	<table><tr><td rowspan="5">REVISED</td><td rowspan="5">EC NO: J2013-1512</td><td rowspan="5">2013/06/12</td><td rowspan="5">DRW: NAYOSHI I 01</td><td rowspan="5">2013/06/12</td><td rowspan="5">CHKD: KATAHASHI</td><td rowspan="5">2013/06/12</td><td rowspan="5">APPR: YNOGAWA</td><td rowspan="5">2013/06/25</td><td rowspan="5">DESCRIPTION</td><td rowspan="5">REV</td><td>QUALITY SYMBOLS</td><td rowspan="5">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE</td><td>SCALE</td><td>DESIGN UNITS</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>MM ONLY</td><td>NTS</td><td>METRIC</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY</td><td>DATE</td><td rowspan="3">TITLE</td></tr><tr><td></td><td></td><td></td><td>CHECKED BY</td><td>DATE</td></tr><tr><td></td><td></td><td></td><td>APPROVED BY</td><td>DATE</td></tr><tr><td colspan="12">A4</td><td></td><td>ANGULAR ± 3 °</td><td>MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td>SHEET NO.</td></tr><tr><td colspan="12"></td><td></td><td>DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-78119-001</td><td>6 OF 7</td></tr><tr><td colspan="12"></td><td></td><td></td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>										REVISED	EC NO: J2013-1512	2013/06/12	DRW: NAYOSHI I 01	2013/06/12	CHKD: KATAHASHI	2013/06/12	APPR: YNOGAWA	2013/06/25	DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		MM ONLY	NTS	METRIC		mm	INCH	DRAWN BY	DATE	TITLE				CHECKED BY	DATE				APPROVED BY	DATE	A4													ANGULAR ± 3 °	MATERIAL NO.	DOCUMENT NO.		SHEET NO.														DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE		SD-78119-001		6 OF 7															THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					A																																																																																																																																																																															
REVISED	EC NO: J2013-1512	2013/06/12	DRW: NAYOSHI I 01	2013/06/12	CHKD: KATAHASHI	2013/06/12	APPR: YNOGAWA	2013/06/25	DESCRIPTION	REV												QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE		DESIGN UNITS	THIRD ANGLE PROJECTION																																																																																																																																																																																																																																																										
																									MM ONLY	NTS	METRIC																																																																																																																																																																																																																																																													
																									mm	INCH	DRAWN BY		DATE		TITLE																																																																																																																																																																																																																																																									
																											CHECKED BY		DATE																																																																																																																																																																																																																																																											
														APPROVED BY	DATE																																																																																																																																																																																																																																																																									
A4													ANGULAR ± 3 °	MATERIAL NO.	DOCUMENT NO.		SHEET NO.																																																																																																																																																																																																																																																																							
													DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE		SD-78119-001		6 OF 7																																																																																																																																																																																																																																																																						
														THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																																																																																																																																																										
	ib_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																														

