





JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF22140-24B	LCD HIGH OUTPUT WHITE 8400°k RGB	730 @ 0°C	340	5	38,000 ± 10%	20,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION											
					TITLE													
					MINIATURE COLD CATHODE FLUORESCENT LAMP													
A			DIM LINE CORRECT. AND 140 +/- 5.0 TO 140 +/- 3.0		10/17/00		SIZE		FSCM NO.		DRAWING NO.							
			RELEASED		6/7/00		A		55335		BF22140-24B							
REV. NO.			DESCRIPTION/ECO NUMBER		APP'D DATE		- CAD DRAWING -		SCALE		RELEASED DATE		REVISION DATE		REV. NO.		SHEET	
							MANUAL REVISIONS NOT PERMITTED		NONE		6/7/00		10/17/00		A		1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF22140-24B](#)