



## XTRAFLEX Liquidtight Conduit Tubing & Fittings

### T&B Catalog Number:

**UPC Number:** LTC050  
**Status:** 78621078954  
**Description:** Active

1/2 in. black non-metallic Type B industrial grade liquidtight conduit.

#### Features

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.

#### Application

Machine tools, motor hookups, food processing equipment, extensions from wire ways, and sensor and micro switch wiring found in control consoles.  
UL Listed for direct burial

#### General

Material	PVC
Color	Black
Working Temperatures	-18 C to +105 C

#### Dimension Information

Size (inches)	1/2
I.D. - Minimum (inches)	0.622
I.D. - Maximum (inches)	0.642
O.D. - Minimum (inches)	0.82
O.D. - Maximum (inches)	0.84

#### Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	13.13 lbs. per 100

#### Application Support

Guide to Nonmetallic Conduit Applications Available on Website	
XTRAFLEX System Specifications	Available on Website

#### Certifications

RoHS Compliance	Yes
-----------------	-----

#### Certifications



File Nbr:  
E 95745

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)