



FEATURES:

- The molded strain relief is tightly bonded to the cable jacket for superior strength and durability.
- Gold plated center contacts assure the most noise free connection possible.
- The connectors and cable are selected for the best performance possible.
- Teflon insulation and tarnish resistance outer shells provide the longest lifetime of any cable assembly available.
- For use below 50 VDC (75 VAC) when hand contact is possible.
- Maximum useful voltage is 500 V.

MATERIALS:

BNC Connector: Body – Brass, Nickel Plated
 Center Conductor – Brass, Gold Plated
 Impedance: 50 Ohms

UHF Connector: Body – Brass, Nickel Plated
 Center Conductor – Brass, Gold Plated
 Impedance: Non-Constant

Strain Relief Boot: PVC, Color - Black

Cable: RG58C/U, 50 Ohm impedance, .195 (4.95mm) O.D. Marking: "POMONA 1367-C-XX"

RATINGS:

Operating Voltage: 500 VRMS
 Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 1367-C-XX

XX = Length in inches. Std. Lengths: 18" (45.72cm), 24" (60.96cm), 36" (91.44cm), 48" (121.92cm) & 60" (152.40cm). Additional lengths can be ordered upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1367-C-48](#) [1367-C-36](#) [1367-C-60](#) [1367-C-24](#) [1367-C-18](#)