


REV.	DATE	ECR NO.	DESCRIPTION
NC	03/16/09	XXXXXX	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	CW	08/25/09							
7						CHECKED				PART DESCRIPTION N MALE TO MALE ADAPTOR					
6						ISSUED									
5	RETAINER RING	SUS 304	NATURAL	2		SHEET	1 OF 1				PART NO. 172122				
4	GASKET	SILICONE	RED	2											
3	CONTACT PIN	BRASS	GOLD	1						DWG. NO. 172122.DWG					
2	INSULATOR	PTFE	NATURAL	1											
1	BODY	BRASS	NEXCOTE	1						REV.	NC	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/CONNEX/172122.DWG									