

**3M™ Cubitron™ II Abrasives**[Products](#) | [Technology](#) | [Resources](#) | [Testimonials](#) | [Videos](#)[United States](#) > [Products & Services](#) > [Manufacturing and Industry](#) > [Cubitron II](#) > [Products](#) > [Cable/Wire](#) > **3M™ Round, Shielded/Jacketed, Flat Cable, 3659 Series 3659/26, 100 ft.**3M™ Round, Shielded/Jacketed, Flat Cable, 3659 Series 3659/26, 100 ft.  
UPC# 00051138420598 3M Product Number 3659/26 3M ID 80610802235[Print](#) [Share](#) .050" 28 AWG Stranded, Mass Terminatable, PVC/PVC, 100 ft.

- Round construction permits easier routing
- 28 AWG wire on .050 inch pitch permits mass termination to broad line of IDC connectors
- Continuous split/bond repeat allows for mass termination on 2.4 inch centers (approximate)
- Primary cable is zippable for branching or discrete terminations
- Meets external wiring requirements of National Electrical Code, Article 725 (CL2)
- UL listed for USA and Canadian markets
- Dual shielding provides 35 db average shielding effectiveness
- RoHS Compliant

**Need Help?****Questions?** We can help  
[Contact Us](#) Network Access Message: The page[Overview](#) [Support](#)**Specifications****Color**

Gray

**Shape**

Round

**People who viewed this item also viewed**

3M™ High Flex Life Cable, 3319 Series, 3319/16, 100 ft.



3M™ 4-Wall Header .100 in., High Temp Option, Right Angle, 50 Contacts, 3433-5000



3M™ 4-Wall Header .100 in., High Temp Option, Straight, 16 Contacts, 3408-6002



3M™ Round Conductor Flat Cable, 3365 Series, 3365/40, 100 ft.



3M™ Four-Wall Header, 3000 Series, 3314-5303

