

Current refinements (click  to remove)

[Search Tips](#) 
 [Region](#)  [USA](#)  [Product Family](#)  [Code Conductor, Two-Hole, Long Barrel Lug](#)  [Text Search: 'LCC2-38D-Q'](#)


For Use with Stranded Copper Conductors

- Long barrel maximizes number of crimps and provides premium wire pull-out strength and electrical performance
- Color-coded barrels marked with **PANDUIT** and specified competitor die index numbers for proper crimp die selection
- Enclosed barrel prevents corrosive material from entering barrel when used in harsh environments
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with **PANDUIT** and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range-taking capability when crimped with **PANDUIT® Uni-Die™** Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved
- Available with NEMA hole sizes and spacing

Part Number:	LCC2-38D-Q
RoHS Compliance Status:	Compliant
Part Description:	Two-hole, long barrel lug, #2 AWG wire, 3/8" stud hole, 1" hole spacing.
Product Type:	Compression Connectors - Lugs
CSA Certified:	Yes
UL Listed:	Yes
Length (In.):	3.34
Length (mm):	84.8
Copper Conductor Size:	#2 AWG
Stud Hole Size (In.):	3/8
Stud Hole Spacing (In.):	1.00
Tongue Width (In.):	.66
Barrel Length (In.):	1.16
Angle:	Straight
Clearance:	.47
Figure No.:	1
Panduit Color Code:	Brown
Panduit Die Index No.:	P33
Tongue Thickness:	.10
Tongue Type:	Standard
Tongue Width (mm):	16.8
Wire Range (mm ²):	35
Wire Strip Length (In.):	1 1/4
Min. Order UOM:	PC
Min. Order Qty.:	1
Burndy Die Index No.:	10
T&B Die Index No.:	33

Related Products


- [Contour Crimp™ Control...](#)
- [Die Type, Manual, Crimping Tool](#)
- [CD-720 Crimping Dies](#)
- [Die Type, Manual Hydraulic, 14 Ton,...](#)
- [Die Type, Remote Hydraulic, 14 Ton,...](#)
- [Die Type, Battery Powered Hydraulic...](#)
- [More...](#)

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-1/4 in.
Stud Size	3/8 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90 ° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



CERTIFIED

LISTED
Wire Connector



00	12/02	SAB	DRL	RELEASED	10333	PANDUIT	CORP. TINLEY PARK, ILLINOIS
REV	DATE	BY	CHK	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FILE LCC2-38D-CUST

LCC2-38D-Q
Copper Lug - Two-Hole, Long Barrel