


Waterproof Bat Handle Toggle




Features

- **Waterproof:** IP56
- **Single Pole Types**
- **Internal "O" Ring for Moisture and Dust Resistance**
- **.250" Quick Connect Terminals**



S115



Specifications

Current Rating:

A: 16A 277VAC, 1 HP

B: 20A 277VAC, 1 HP

Insulation Resistance: 100 Megohms (min.) at 500VDC

Dielectric Strength: 1500V RMS (min.)

Temperature Rating: +32°F to +149°F (0°C to +65°C)

Electrical Life: 6,000 cycles

Mechanical Life: 10,000 cycles at full load

Terminal Type: Refer to Diag No. in Table

Mounting Hole: .472 (12.0)

	NTE Type No.	Circuitry	Current Rating	Action			Actuator	Diag No.
NEW	54-348W#	SPST	B	ON	NONE	OFF	Brass/Nickel Plate	S115b
NEW	54-349W	SPDT	A	ON	NONE	ON	Brass/Nickel Plate	S115b
NEW	54-350W	SPDT	A	ON	OFF	ON	Brass/Nickel Plate	S115b
NEW	54-352W	SPDT	A	(ON)	OFF	(ON)	Brass/Nickel Plate	S115b
NEW	54-354W	SPST	B	ON	NONE	OFF	Brass/Nickel Plate	S115c
NEW	54-355W	SPDT	A	ON	NONE	ON	Brass/Nickel Plate	S115c
NEW	54-356W	SPDT	A	ON	OFF	ON	Brass/Nickel Plate	S115c
NEW	54-358W##	SPDT	A	(ON)	OFF	(ON)	Brass/Nickel Plate	S115c

SPECIAL NOTE: () = Momentary Function

UL for 16 Amp **ONLY**


UL for 12 Amp **ONLY**

Waterproof Bat Handle Toggle




Features

- **Waterproof:** IP56
- **Double Pole Types**
- **Internal "O" Ring for Moisture and Dust Resistance**
- **.250" Quick Connect Terminals**



S114



Specifications

Current Rating:

A: 16A 277VAC, 1 HP

B: 20A 277VAC, 1 HP

Insulation Resistance: 100 Megohms (min.) at 500VDC

Dielectric Strength: 1500V RMS (min.)

Temperature Rating: +32°F to +149°F (0°C to +65°C)

Electrical Life: 6,000 cycles

Mechanical Life: 10,000 cycles at full load

Terminal Type: Refer to Diag No. in Table

Mounting Hole: .472 (12.0)

	NTE Type No.	Circuitry	Current Rating	Action			Actuator	Diag No.
NEW	54-360W	DPDT	A	ON	NONE	ON	Brass/Nickel Plate	S114b
NEW	54-361W	DPDT	A	ON	OFF	ON	Brass/Nickel Plate	S114b
NEW	54-364W	DPDT	A	(ON)	OFF	(ON)	Brass/Nickel Plate	S114b
NEW	54-366W##	DPST	B	ON	NONE	OFF	Brass/Nickel Plate	S114b
NEW	54-367W##	DPST	B	ON	NONE	OFF	Brass/Nickel Plate	S114c
NEW	54-369W	DPDT	A	ON	NONE	ON	Brass/Nickel Plate	S114c
NEW	54-370W##	DPDT	A	ON	OFF	ON	Brass/Nickel Plate	S114c
NEW	54-373W	DPDT	A	(ON)	OFF	(ON)	Brass/Nickel Plate	S114c

SPECIAL NOTE: () = Momentary Function

UL for 12 Amp **ONLY**