

K DETAIL 2 : 1





示意图 SCHEMATIC

安装孔 PIERCING PLAN

规格 Specifications

额定负荷 Ratings	DC 30 V 0.3 A
初期接触电阻 Initial Contact Resistance	20 mΩ Max.
绝缘电阻 Insulation Resistance	DC 500 V 60±5 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 500 V (50~60Hz) 60±5 Sec.

操作力 Operating Force (gf)	A → B	B → A
	250±100	250±100
负荷寿命 Operating Life With Load	10,000 次	Cycles

6	端子 TERMINAL	C2680R	3	Ag PLATED
5	基板 TERMINAL BASE	PHENOL RESIN	1	YELLOW
4	接触片 CONTACT	C5210R	1	Ag CLAD
3	弹片 SPRING PLATE	SUS	1	NATURAL
2	胶柄 KNOB	PA	1	VG 2-8
1	铁壳 FRAME	S P C C	1	Sn PLATED
序号	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE	DWG NO. ITEM2691	

TOLERANCES UNLESS OTHERWISE SPEC.

UNDER 1	± 0.10
1 - 10	± 0.30
OVER 10	± 0.50

TITLE

DRAWN

SLIDE SWITCH

ITEM NO

SS-12D07-VG

GA PA

VERSION

A01

PAGE


1 OF 1

SCALE

UNIT

mm

PROJECTION



COMAX

ELECTRONICS (HUIZHOU) CO., LTD.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[SS-12D07-VG 4 NS GA PA](#)