

MICRO SWITCH


FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-R2439-P4

AGH9538




3X 8-32 UNC (.219) BINDING
HEAD COMBINATION TERMINAL
SCREW AND CUPWASHER

NOTE -

- △ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ±.002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 7-10 OZ
DIFFERENTIAL FORCE --- 1/2 - 1 1/4 OZ

DIFFERENTIAL TRAVEL ---- .0005 MAX
OVERTRAVEL ----- .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P O T

L103 15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC (T)
L288
L306
L310
L315
16A 250V ~ T85 5E4



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DES.	TOL.	DES.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/64	X	0.015
ONE PLACE	X,X	0.015	X,X	0.015
TWO PLACES	X,X,X	0.005	X,X,X	0.005
THREE PLACES	X,X,X,X	0.001	X,X,X,X	0.001
ANGLES				

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .074 LB

CATALOG LISTING

BZ-R2439-P4

PAGE 1 OF 1

M

ISSUE

7

RELEASE NO. PR-15688

12SEP07

PSR

CHECK

REVISIONS

A	CO-73287-G	20 OCT 93	JAT
B	CO-75367B	3 MAR 94	SAV
C	CO-77863	6 J W	10 MAY 96
D	203155	C S L	24 MAY 01
E	0018686	TGP	18 FEB 06
F	0033748	BS	12SEP07

18 FEB 06

RJ

CHECK

87

JUN

MAM

CHECK

12 JUN 87

TPS

RASTER

FO-52848-A

DRAWN