




MATERIAL: HOUSING: GLASS FILLED THERMOPLASTIC, UL 94V-0, BLACK
CONTACT: HIGH PERFORMANCE COPPER ALLOY

PLATING: GOLD FLASH OVER 50 MICRO-INCH NICKEL UNDERPLATE

ELECTRICALS: CURRENT RATING: 1.0 AMPERE MAX.
CONTACT RESISTANCE: 30 MILLIOHM MAX.
DMV: 500 Vrms MIN.
INSULATION RESISTANCE: 1 X 10⁴ MOHMS
OPERATING TEMP: -55°C TO 105°C

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.			
	DRAWN: PAM JENKINS	DATE: 12-13-01		
CHECKED:		DATE:		
SCALE:	SHEET 1	OF 1	REV 1	
DWG NO. 800-002-SP2-001				