


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART NUMBER | STUD SIZE | WIRE RANGE AWG | DIMENSIONS (in.)  |                   |                   |                   |                   |
|-------------|-----------|----------------|-------------------|-------------------|-------------------|-------------------|-------------------|
|             |           |                | A <sup>±.03</sup> | W <sup>±.01</sup> | C <sup>±.01</sup> | M <sup>±.02</sup> | H <sup>±.02</sup> |
| PN22-2F     | #2        | #26-22         | .66<br>(16.76)    | .20<br>(5.08)     | .19<br>(4.85)     | .56<br>(14.22)    | .09<br>(2.28)     |

## NOTES

1. RECOMMENDED FOR:
  - A. 300V MAX. VOLTAGE RATING
  - B. #26-22 AWG SOLID OR STRANDED  
COPPER WIRE
  - C. 221°F (105°C) MAX TEMP. RATING
2. MATERIAL:
  - A. STAMPING: .020 (0.51) THK COPPER,  
TIN PLATED.
  - B. HOUSING: YELLOW NYLON
  - C. SLEEVE: TIN PLATED BRASS
3. PACKAGE QUANTITY:   -C = 100  
                                  -M = 1000
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-520, CT-1525
6. WIRE STRIP LENGTH : 3/16 <sup>+1/32</sup><sub>-0</sub> (4.76 <sup>+0.8</sup><sub>-0</sub>)



A41234\_01

|     |      |     |     |                    |       |    |      |    |     |  <b>PANDUIT</b> CORP.      TINLEY PARK, ILLINOIS |       |       |             |
|-----|------|-----|-----|--------------------|-------|----|------|----|-----|---------------------------------------------------------------------------------------------------------------------------------------|-------|-------|-------------|
| 01  |      | JKD |     | ADDED CT-1525 TOOL |       |    |      |    |     | #26-22 BARREL NYLON INSULATED FORK                                                                                                    |       |       |             |
| 00  | 7/97 | TM  | RLS | RELEASED           | 06083 |    | LCA  | RM |     |                                                                                                                                       |       |       |             |
| REV | DATE | BY  | CHK | DESCRIPTION        | ECN # | QA | CUST | PM | APP | DRAWN BY                                                                                                                              | CHK'D | SCALE | DRAWING NO. |
|     |      |     |     |                    |       |    |      |    |     | TSPA                                                                                                                                  | RLS   | NONE  | A41234      |