


Nylon Round Spacers



- Molded nylon 6/6.
- An excellent insulator, the nylon spacer's surface lubricity allows wires to be routed against spacer without fear of chafing the insulation.
- Natural (milky white) finish.
- Relatively low operating temperature.

SCREW NO.	MAJOR DIA.	HOLE SIZE
#2	0.086	0.093
#3	0.099	0.100
#4	0.112	0.120
#5	0.125	0.130
#6	0.138	0.144
#8	0.164	0.169
#10	0.190	0.196
#12	0.216	0.220

LENGTH		O.D.	HOLE CLEARANCE SIZE					LENGTH		O.D.	HOLE CLEARANCE SIZE				
			#2	#4	#6	#8	#10				#2	#4	#6	#8	#10
0.125	1/8	3/16	9160	9180				.562	9/16	5/16		4065H	4067H	4069H	
		1/4		4000	4001	4002				3/8			4068H	4070H	
		5/16			4065A	4067A	4069A			3/16	9168	9188			
		3/8				4068A	4070A			1/4		4024	4025	4026	
0.187	3/16	3/16	9161	9181				.625	5/8	5/16		4065J	4067J	4069J	
		1/4		4003	4004	4005				3/8			4068J	4070J	
		5/16			4065B	4067B	4069B			3/16	9169	9189			
		3/8				4068B	4070B			1/4		4027	4028	4029	
0.25	1/4	3/16	9162	9182				.687	11/16	5/16		4065K	4067K	4069K	
		1/4		4006	4007	4008				3/8			4068K	4070K	
		5/16			4065C	4067C	4069C			3/16	9170	9190			
		3/8				4068C	4070C			1/4		4030	4031	4032	
0.312	5/16	3/16	9163	9183				.750	3/4	5/16		4065L	4067L	4069L	
		1/4		4009	4010	4011				3/8			4068L	4070L	
		5/16			4065D	4067D	4069D			3/16	9171	9191			
		3/8				4068D	4070D			1/4		4033	4034	4035	
0.375	3/8	3/16	9164	9184				.812	13/16	5/16		4065M	4067M	4069M	
		1/4		4012	4013	4014				3/8			4068M	4070M	
		5/16			4065E	4067E	4069E			3/16	9172	9192			
		3/8				4068E	4070E			1/4		4036	4037	4038	
0.437	7/16	3/16	9165	9185				.875	7/8	5/16		4065N	4067N	4069N	
		1/4		4015	4016	4017				3/8			4068N	4070N	
		5/16			4065F	4067F	4069F			3/16	9173	9193			
		3/8				4068F	4070F			1/4		4039	4040	4041	
0.5	1/2	3/16	9166	9186				.937	15/16	5/16		4065P	4067P	4069P	
		1/4		4018	4019	4020				3/8			4068P	4070P	
		5/16			4065G	4067G	4069G			3/16	9174	9194			
		3/8				4068G	4070G			1/4		4042	4043	4044	
0.562	9/16	3/16	9167	9187			1	1	5/16		4065Q	4067Q	4069Q		
		1/4		4021	4022	4023				3/8			4068Q	4070Q	