


12 CKT ISO
SHOWN FOR
REF ONLY



1. MATERIAL:

OPTION 1: POLYESTER, UL 94 V-0, COLOR: BLACK
OPTION 2: LIQUID CRYSTAL POLYMER, GLASS FILLED, UL94 V-0, COLOR: BLACK
PIN: .025/0.64 SQ PIN: COPPER ALLOY

2. FINISH:

FOR ADDITIONAL PLATING INFORMATION SEE SDES-88.
(154)/ - OVERALL TIN: .000100/0.00254 MIN. OVER NICKEL: .000050/0.00127 MIN.
(222)

(208) - SELECT GOLD: .000015/0.00038 MIN.
SELECT TIN: .000100/0.00254 MIN.
WITH OVERALL NICKEL UNDERPLATE: .000050/0.00127 MIN.


(228) - SELECT GOLD: .000030/0.00076 MIN.
SELECT TIN: .000100/0.00254 MIN
WITH OVERALL NICKEL UNDERPALTE: .000050/0.00127 MIN.

THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS"
DIRECTIVE 2002/95/EC 'AND ELV ANNEX II OF DIRECTIVE 2000/53/EC, AND
CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD PLATING.

3. PRODUCT SPECIFICATION: NONE

4. PACKAGING INFORMATION: PK-68312-001

5. PARTS ARE NOT STACKABLE ON .100/2.54 CENTERS



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: 1.57/.062

F

L

1

0

E

A

